


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/08/2020	GUTTADAURO
B	ECN 11058: REVISED TRIANGLES IN PORT 4	03/29/2021	GUTTADAURO



NOTES:

1. LABEL PER ILS-100-03. FOR INTERNAL REFERENCE ONLY. LABEL LOCATION FOR REFERENCE ONLY.

INTERFACE:

1. 8X 10/100/1000BASE TX TRIPLE SPEED PORT, RJ45 FEMALE
2. 4X 802.3AT POE+ PORTS, RJ45 FEMALE
3. TOTAL PORTS: 8

POWER:

1. POWER REQUIREMENTS: 48-56V, 1.5A MAX
2. POWER CONSUMPTION: 70W / 239BTU
3. POE STANDARD: IEEE 802.3AT, POE+ (BACKWARDS COMPATIBLE WITH IEEE 802.3AF)
4. POE TYPE: END-SPAN PSE
5. POWER PIN ASSIGNMENT: 1/2 (+), 3/6 (-)
6. POE POWER BUDGET 60W

ENVIRONMENTAL:

1. OPERATING TEMPERATURE: -10°C - 60°C
2. STORAGE TEMPERATURE: -20°C - 70°C
3. RELATIVE HUMIDITY: 5% - 95% (NON-CONDENSING)
4. METAL ENCLOSURE: IP30

INSTALLATION OPTIONS:

1. DIN-RAIL
2. WALL MOUNT
3. MAGNETIC MOUNT

DIP SWITCH (PLEASE REBOOT SWITCH AFTER ADJUSTING DIP SWITCH)


1. STANDARD: ALL PORTS OPERATE AT 10/100/1000MBPS AUTO-NEGOTIATION
2. VLAN: PORTS 1 THRU 6 ISOLATE & ONLY COMMUNICATE WITH PORTS 7 & 8
3. EXTEND: PORTS 1 THRU 6 ISOLATE & ONLY COMMUNICATE WITH PORTS 7 & 8 WITH 22-25W POE TRANSMIT DISTANCE OF 250M AT REDUCED SPEED OF 10MBPS

PACKAGE CONTENTS:

- GIGABIT SWITCH
- WALL MOUNT KIT (NOT SHOWN)
- MAGNET KIT (NOT SHOWN)
- RJ45 DUST CAPS (NOT SHOWN)
- POWER ADAPTER + POWER CORD (NOT SHOWN)
- DIN-RAIL MOUNT KIT (NOT SHOWN)

D
C
B
A

D
C
B
A



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCES:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2 [51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ± .2 [5] | FRACTIONS ± 1/32
 .XX = ± .02 [5] | ANGLES ± 1°
 .XXX = ± .005 [13] | ANGLES ± 1°

THIRD-ANGLE PROJECTION

APPROVALS	DATE
DRAWN BY DZINN	09/08/2020
CHECKED BY DFRISIELLO	09/08/2020
APPROVED BY GUITA DAURO	09/08/2020

L-com
an INFINIT® brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY
NETWORK EQUIPMENT


PRODUCT DESCRIPTION
8 Port Wall Mount Gigabit Ethernet Switch w/ PoE+

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	WM8-4G-4GP+	B
SCALE: NONE		CAD FILE: WM8-4G-4GP+.SLDDRW	SHEET 1 OF 2

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

LABEL PER ILS-100-03
SEE NOTE 1



PRODUCT INFORMATION LABEL

BACK VIEW

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY NETWORK EQUIPMENT			
PRODUCT DESCRIPTION 8 Port Wall Mount Gigabit Ethernet Switch w/ PoE+			
SIZE A	CAGE CODE 43321	ITEM NO. WM8-4G-4GP+	REV. B
SCALE: NONE		CAD FILE: WM8-4G-4GP+.SLDDRW	
			SHEET 2 OF 2