

Floor Cabinets - Quick Assemble



L-com's Network Cabinets are the perfect solution to install your large or small networking equipment in limited spaces. They can also be built in place for spaces where a fully-assembled cabinet cannot be brought in. It's accommodating, sleek design is compatible with most standard 19-inch rackmount equipment and accessories. These Network Cabinets are equipped with lockable doors and panels offer easy access to cables and equipment, while providing a secure cabinet for your network equipment

Model/SKU		LCSN066627	LCSN066827
PHYSICAL			
Rack Capacity (in Rack Units)		27U	27U
Unit Dimensions (in)	H	54.74	54.74
	W	23.7	23.7
	D	23.7	31.5
Weight Capacity (kg/ lbs.)		800kg/1763lbs	800kg/1763lbs
Front Door		Tempered glass door with lock	
Rear Door		Solid steel door with lock	
Side panels		2pcs removable steel side panels with locks and latches	
Top Panel		Cable entry covers and Fan tray compatible (purchased separately)	
Bottom Panel		Cable entry covers	
Material		Cold Rolled Steel	
Painting/ Coating		Electro-static Powder Coating - Black	
Construction		Bolted - Quick Assembly (~15min, 1 person)	
Rail Thread Type		Square hole/Cage Nut	
ADDITIONAL FEATURES			
Equipment Mounting Hardware		M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)
Mounting		Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)
Assembly		Assembly required	
COMPATIBILITY AND STANDARDS			
EIA/ECA-310-E		✓	
CE		✓	
PCI		✓	
HIPPA		✓	
NEMA TYPE-1 PROTECTION		✓	
IP 20 PROTECTION		✓	
ROHS & REACH		Please contact our customer service team at sales@navepoint.com	
SHIPPING			
Shipping Dimensions (in)	L	52.4	52.4
	W	24	24
	H	24.4	32.3
Shipping Weight (lbs.)		141.32	193.57

Floor Cabinets - Quick Assemble



Our Network Cabinets are the perfect solution to install your large or small networking equipment in limited spaces. They can also be built in place for spaces where a fully-assembled cabinet cannot be brought in. It's accommodating, sleek design is compatible with most standard 19-inch rackmount equipment and accessories. These Network Cabinets are equipped with lockable doors and panels offer easy access to cables and equipment, while providing a secure cabinet for your network equipment.

Model/SKU	LCSN066627W	LCSN066632W	LCSN066637W	LCSN066832W	LCSN066837W	LCSN066632	LCSN066637	LCSN066832	LCSN066837	
PHYSICAL										
Rack Capacity (in Rack Units)		27U	32U	37U	32U	37U	32U	37U	32U	37U
Unit Dimensions (in)	H	54.74	63.5	72.24	63.5	72.24	63.5	72.24	63.5	72.24
	W	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
	D	23.7	23.7	23.7	31.5	31.5	23.7	23.7	31.5	31.5
Weight Capacity (kg/ lbs.)		800kg/1763lbs	800kg/1763lbs	800kg/1763lbs	800kg/1763lbs	800kg/1763lbs	800kg/1763lbs	800kg/1763lbs	800kg/1763lbs	800kg/1763lbs
Front Door		Tempered glass door with lock								
Rear Door		Solid steel door with lock								
Side panels		2pcs removable steel side panels with locks and latches								
Top Panel		Cable entry covers and Fan tray compatible (purchased separately)								
Bottom Panel		Cable entry covers								
Color	White	White	White	White	White	Black	Black	Black	Black	
Material	Cold Rolled Steel									
Painting/ Coating	Electro-static Powder Coating									
Construction	Bolted - Quick Assembly (~15min, 1 person)									
Rail Thread Type	Square hole/Cage Nut									
ADDITIONAL FEATURES										
Equipment Mounting Hardware	M6 screws/cagenuts (Qty 20 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	M6 screws/cagenuts (Qty 30 ea)	
Mounting	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	Floor (Includes casters/leveling feet)	
Assembly	Assembly required									
COMPATIBILITY AND STANDARDS										
EIA/ECA-310-E	✓									
CE	✓									
PCI	✓									
HIPPA	✓									
NEMA TYPE-1 PROTECTION	✓									
IP 20 PROTECTION	✓									
ROHS & REACH	✓									
SHIPPING										
Shipping Weight (lbs.)	141.3	154.54	170.42	169.3	193.57	154.54	170.42	169.3	193.57	