

16x14x04 UL Listed Polycarbonate Slimline Weatherproof Outdoor IP68 NEMA 6P Enclosure

NBPCSL161404



Features

- High-Impact, UV Resistant Polycarbonate
- Shallow depth design with Industry standard height/width
- NEMA Type 6P/ IP68* rated
- Non-metallic cover latches and padlock hasp
- Fully gasketed lid & Molded-In Mounting Feet (includes (4x) optional lid corner screws)
- Back panel Mounting Hardware included

Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage

Description

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from High-Impact, UV Resistant Polycarbonate material that provides superior durability to impacts and ease of modification while maintaining minimum weight. It is well suited for high temperature or corrosive environments. The shallow depth design while maintaining industry standard height/width dimensions is ideal for low profile applications.

Molded-In Mounting feet allow the enclosure to be mounted directly to any flat wall surface provided proper screws are used into secure studs.

The Mounting feet have a slotted opening design and (with minor modification to enlarge the opening for the hardware) can also be used with our HGX-PMT pole mount kits.

Compatible versions include HGX-PMT13, HGX-PMT16, HGX-PMT28, HGX-PMT29, HGX-PMT30, & HGX-PMT33

The lid features a non-metallic hinge system that allows for quick removal & can be reattached just as quickly without the need for any tools. The Lid also comes with a non-metallic locking hasp to secure the enclosure from tampering.

Brass inserts included for mounting a backplate. Both Aluminum (HGX-NPLATE26) and Non-Metallic (HGX-NPLATE27) backplates are available (sold separately). Built-in DIN rail mounting embosses on the inside back wall provide multiple mounting hole positions to accommodate your unique DIN rail install requirements minimizing the need for on-site modifications. The recommended hardware for mounting to these mounting embosses is #10-14 Phillips Rounded Head Thread-Forming Screws for Plastic, 18-8 Stainless Steel, 1/4" Long.

*Note: Any holes or openings you might introduce must be properly sealed to maintain NEMA Type 6P / IP68 rating

Mechanical Specifications

Size

Outer Height	19.3 in	[490.22 mm]
Outer Width	16.7 in	[424.18 mm]
Outer Depth	5.4 in	[137.16 mm]
Inner Height	16.2 in	[411.48 mm]
Inner Width	14.2 in	[360.68 mm]
Inner Depth	5.1 in	[129.54 mm]
Weight	6.4 lbs	[2.9 kg]

Environmental Specifications

Temperature Rating	-40° to 248°F [-40° to 120°C]
Ingress Protection (IP) Rating	IP68
NEMA Rating	6P
Flammability Rating	UL94-5VA
Outdoor UV Exposure	(UL 746C) (f1) Rated

16x14x04 UL Listed Polycarbonate Slimline Weatherproof Outdoor IP68 NEMA 6P Enclosure

NBPCSL161404



Compliance Certifications

UL Listed

E541342

16x14x04 UL Listed Polycarbonate Slimline Weatherproof Outdoor IP68 NEMA 6P Enclosure from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/16x14x04-inch-ul-listed-polycarbonate-slim-weatherproof-outdoor-ip68-nema-6p-enclosure-nbpcsl161404-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

16x14x04 UL Listed Polycarbonate Slimline Weatherproof Outdoor IP68 NEMA 6P Enclosure

