THE INFORMATION CONTAINED IN THIS PROPERTY OF L-COM, INC. ANY REPROD WITHOUT THE WRITTEN PERMISSION OF L-COM DESCRIPTION M/	DRAWING IS THE SOLE DUCTION IN PART OR WHOLE COM, INC. IS PROHIBITED.						REVISIONS			-
	COM, INC. IS PROHIBITED.				RE	V	DESCRIPTION	DATE	APPROVED	-
	WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.				В	ECN 5401: REDRAWN	O NEW FORMAT & SUPPLIER SPECS	3/22/11	D. CASTRO	1
					С	ECN 6006: CHANGED	PIN CRIMP TO .047	3/2/12	D.FRISIELLO	-
	ATERIAL FINISH									-
	BRASS NICKEL									1
										D
	PTFE									
	BRASS GOLD			.65			/	aa \		
	BRASS NICKEL			$- \left(\begin{array}{c} .65\\ [16.6] \end{array} \right) - $				33	-	
NUT E	BRASS NICKEL							.0] /		
								_		
										F
					0			ຈ ໂ ∭		
С								/		C
	I									
047							.41			
▶ [1.19]]	<u> </u>						[10.5]			
<u> </u>	.213									
	[5.41]						.12			
≜							[3.0]			
	4							.09		
В								[2.3]]	В
RECON	MMENDED	RECOMMENDE	D					[2.0]]	
PIN	CRIMP	FERRULE CRIMF	0							
						/				
						/				
NOTES:										
							RECOMMENDED			
ELECTRICAL:					4		CABLE STRIPPING			
IMPEDANCE: 50 OHM VOLTAGE RATING: 50	IS In volts peak			RoHS Complia						
FREQUENCY RANGE:	DC ~ 2 GHz			UNLESS OTHERWISE SPECIFIED,	APPR	ovals date		45 BEECH	WOOD DRIVE	1
DIELECTRIC WITHSTAN	DING VOLTAGE: 1000 \	volts RMS		DIMENSIONS ARE IN INCHES [mm]	DRAWN BY			NORTH AI	NDOVER, MA	
A INSERTION LOSS: .20dE A CABLE RETENTION: 30				OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0	B. PUCHA CHECKED B	Y		0	1845	•
A CABLE RETENTION: 30	TOUNDS FULL			212 [305] =+1 [25] /-0 >12 [305] ≤60 [1524] =+2 [51] /-0 >60 [1524] ≤120 [3048] =+4 [102] /-0 >120 [3048] ≤300 [7620] =+6 (152) /-0 >300 [7620] =+5% /-0%	B. PUCHA			J		A
MISCELLANEOUS:				>120 [3048] <300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	M. AUDA			\L		-
CONNECTOR SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031				ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$	CON	IFIGURATION DETAILS OF DIMENSIONED FEATURES				
ACCORDANCE WITH APPLICATION: LMR195			.X = ± .2 .XX = ± .02 .XXX = ±.005		MAY VARY	CON,F-TYPE MALE	RG58 CA			
ALL DIMENSIONS ARE FOR REFERENCE ONL		<i>ι</i> .		PROJECTION			SIZE A 55CM NO. DWG. NO. AFM-1700		REV.]
					<u> </u>	1AB13-010	SCALE: NONE CAD FILE: AFM-1700.SI		SHEET 1 OF 1	
°	7	4	5	A	1			1	1	L
8	7	6	Э	4		3	2	1		