$ \begin{array}{c} & \\ & \\ & \\ & \\ & \\ & \\ & \\ & \\ & \\ & $	_	8 7 6		5 😽	4	3		2		1	
$\begin{array}{c c c c c c c c c c c c c c c c c c c $	TI P V	IE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE COPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE ITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.					RELEASE		'ISIONS		-
$ \begin{array}{c} c\\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ $	D	BODYBRASSNICKEL PLATEDCONTACTBRASSGOLD PLATEDINSULATORTFE-		-	.74 [18.7]						
B       Image: Strain St	С		<u>0</u> ]				.43 [11.0	B 0]			
B       FERRULE CRIMP SIZE       CONTACT CRIMP SIZE       CONTACT CRIMP SIZE         RECOMMENDED CABLE STRIPPING         NOTES:         ELECTRICAL:       IMPEDANCE: 50 OHM FREQUENCY RANGE: DC ~ 6 GHz         VOLTAGE RATING: 500 VOLTS PEAK         DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS         MISCELLANEOUS:         APPLICATION: RGS8, WBC/LMR195, BELDEN 8240/8219.         CABLE RETENTION: 30 LBS PULL         COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH J: 2003         COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH J: COMPOCIENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH J: 2003	A	16	.10 [2.5]			[5.41]	Ň	[1.73	} }]		
A       ELECTRICAL: IMPEDANCE: 50 OHM FREQUENCY RANGE: DC ~ 6 GHz VOLTAGE RATING: 500 VOLTS PEAK DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS       UNLESS OTHERWISE SPECIFIED, UNLESS OTHERWISE SPECIFIED, DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS <sup>45</sup> BEECHWOOD DRIVE NORTH ANDOVER, MA 01845         MISCELLANEOUS: APPLICATION: RG58, WBC/LMR195, BELDEN 8240/8219. CABLE RETENTION: 30 LBS PULL          Mortical and the state of t	В	RECOMMENDED CABLE STRIPPING	_				CONTACT	CRIMP SIZE			
A DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS MISCELLANEOUS: APPLICATION: RG58, WBC/LMR195, BELDEN 8240/8219. CABLE RETENTION: 30 LBS PULL COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031				RoHS Compliant 🗸							
APPLICATION: RG58, WBC/LMR195, BELDEN 8240/8219. CABLE RETENTION: 30 LBS PULL COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031	A	IMPEDANCE: 50 OHM FREQUENCY RANGE: DC ~ 6 GHz VOLTAGE RATING: 500 VOLTS PEAK DIELECTRIC WITHSTANDING VOLTAGE: 1000 VOLTS RMS MISCELLANEOUS:		DIME		DRAWN BY D.FRISIELLO	11/10/10 11/10/10 11/10/10		Connectiv	vity NORTH AN	DOVER, MA
		CABLE RETENTION: 30 LBS PULL COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN		ALL OT	HER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005	CONFIGURATION UNDIMENSIONE MAY V	N DETAILS OF ED FEATURES ARY RIATIONS CCUR	W-MALE (W. FO <b>43321</b>	DWG. NO.	C/LMR195 VM-1700	A