


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

**RoHS Compliant** ✓

| REVISIONS |   |          |              |
|-----------|---|----------|--------------|
| REV       | DESCRIPTION   | DATE     | APPROVED     |
| E         | ECN 6492: CHANGED NOTE TO "TDG1026KS-C5E" WITHOUT PKG. UPD LOGO | 10/29/12 | D. DESJARDIN |
|           |   |          |              |
|           |   |          |              |



CAT 5E SHIELDED KEYSTONE FEED-THRU COUPLER (L-COM P/N: TDG1026KS-C5E WITHOUT PACKAGING)

FLANGE MOUNTED KEYSTONE ADAPTOR

KIT SHOWN FULLY ASSEMBLED FOR CLARITY (KIT IS SHIPPED UN-ASSEMBLED)

- KIT INCLUDES:
- 1- SHIELDED COUPLER
  - 1- FLANGE ADAPTOR
  - 1- PACKAGE MOUNTING SCREWS (4-40x 1/4")

**NOTES:**

**MATERIAL:**  
 FLANGED ADAPTOR: ZINC ALLOY  
 HARDWARE: STAINLESS STEEL.

**FINISH:**  
 FLANGED ADAPTOR: NICKEL PLATE.

**MISCELLANEOUS:**  
 VOLTAGE RATING: 36V

**PACKAGING:**  
 KITS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

|  |   |  |  |   |
|--|---|--|--|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +3% / -0%<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ±.2<br>.XX = ±.02<br>.XXX = ±.005 | APPROVALS<br>DRAWN BY<br>D. PARHAM<br>CHECKED BY<br>T. CLARK<br>APPROVED BY<br>C. McCORMICK | DATE<br>4/8/2004<br>4/13/2004<br>4/13/2004 | 45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845 |   |
|  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY                                    |  |  | CATEGORY<br>TELECOM / MODULAR                               |
|  | PROJECTION<br>  | COLOR VARIATIONS MAY OCCUR                 | SIZE<br><b>A</b>                                 | FSCM NO.<br><b>43321</b>                                    |
|  | DWG. NO.<br>ECF504-SC5E   |  | REV.<br><b>E</b>                                 | SCALE: NONE<br>CAD FILE: ECF504-SC5E.SLDDRW<br>SHEET 1 OF 1 |