






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/12/13	B.PUCHASKI



FRONT VIEW
COVER
REMOVED

MOUNTING PLATE
AND SCREWS SHIPPED
LOOSE WITH EACH
ENCLOSURE

NOTES:

- ENCLOSURE MATERIAL-GRAY (RAL7035) HOT MOLDED FIBERGLASS REINFORCED POLYESTER
- NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13 PRIOR TO MODIFICATIONS.
- IEC 529 RATED IP 66 PRIOR TO MODIFICATION.
- TEMPERATURE RANGE FROM -50 DEG C TO 150 DEG C.
- SELF EXTINGUISHING AND HALOGEN FREE.
- CABINETS ARE MAINTENANCE FREE AND CORROSION RESISTANT.
- SHALL BE PACKAGED AS PER L-COM SPEC PKG-00070
- ALL DIMENSIONS FOR REFERENCE ONLY

REGULATORY COMPLIANCE:

RoHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: X = ±.1 XX = ±.01 XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY B.PUCHASKI	06/12/13		
	CHECKED BY P.PESA	06/12/13	CATEGORY ENCLOSURE	
	APPROVED BY P.PESA	06/12/13	PRODUCT DESCRIPTION NEMA ENCLOSURE 16 X 14 X 6 WEATHERPROOF W/BLANK PLATE ALUMINUM	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. NB161406-KIT
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: NB161406-KIT.SLDDRW	REV. A
		SHEET 1 OF 1		