


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/15/07	D.FRISIELLO
B	ECN 2802: REMOVE L-COM LOGO	3/30/07	D.FRISIELLO
C	ECN 6918: UPD FORMAT, PKG, ROHS, REPLACED SLOTTED SCREWS WITH STANDARD	6/26/13	D. DESJARDIN



2X DB25 FEMALE FEED-THRU ADAPTER

- NOTES:**
1. PANEL MATERIAL: .06 [1.5] THK COLD ROLLED STEEL.
 2. PANEL FINISH: FLAT BLACK POWDER COAT.
 3. KIT CONTAINS 4, #6-32 UNC SCREWS.
 4. ASSEMBLED PANEL SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
ROHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $> 12 [305] \leq 60 [1524] = +2 [51] / -0$ $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$ $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +5\% / -0\%$	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	3/15/07		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY P.McNEIL	3/15/07	CATEGORY RACK/ENCLOSURES	
	APPROVED BY J.ROBERTS	3/15/07	PRODUCT DESCRIPTION USP SUB-PNL W/2 DB25 F-F CPLR	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. USP2DB25FB	REV. C
			SCALE: NONE	CAD FILE: USP2DB25FB.SLDDRW
				SHEET 1 OF 1