


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/15/07	D.FRISIELLO
B	ECN 8993: UPDATE LOGO'S AND DIM. FOR COUPLERS. ADD THREAD NOTE	11/15/17	S.LI



NOTES:

1. PANEL MATERIAL: .06 [1.5] THK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. KIT CONTAINS 4, #6-32 UNC SCREWS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.1 [2.5] .XX = ±.01 [.25] .XXX = ±.005 [.13]	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	3/15/07				
	CHECKED BY P.McNIEL	3/15/07	CATEGORY	USP SUB PANEL		
	APPROVED BY J.ROBERTS	3/15/07	PRODUCT DESCRIPTION	USP SUB PANEL, W/2 USB A/B SHIELDED COUPLERS		
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. USP2ECF-UABSB	REV. B
SCALE: NONE			CAD FILE: USP2ECF-UABSB.SLDDRW		SHEET 1 OF 1	