


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/14/07	D.FRISIELLO
A	ECN 99999: REMOVED "SHIELDED" FROM TITLE BLOCK	12/23/08	D.FRISIELLO
B	ECN 5625: ADDED CAT 5E, 1.18 WAS 1.20. ADDED PACKAGING NOTE	7/22/11	D. CASTRO



2X, CATEGORY 5E RJ45 COUPLER

NOTES:

1. PANEL MATERIAL: .06[1.5] THK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. KIT CONTAINS 4, #6-32 UNC SCREWS.
4. PACKAGE IN ACCORDANCE WITH L-COM SPEC. PS-0014

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY P.McNEIL APPROVED BY J.ROBERTS	DATE 3/14/07 3/15/07 3/15/07	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY USP SUB PANEL		PRODUCT DESCRIPTION USP, SUB PANEL W/2 CAT5E COUPLERS	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. USP2MC5B	REV. <b>B</b>
		SCALE: NONE	CAD FILE: USP2MC5B.SLDRW	SHEET 1 OF 1	