


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/2/11	D.GRIFFIN
-	-	-	-



**KIT SHOWN FULLY ASSEMBLED FOR CLARITY
(KIT IS SHIPPED UN-ASSEMBLED)**

NOTES:

1. PANEL MATERIAL: .04 THICK COLD ROLLED STEEL
2. PANEL FINISH: MORTON FLAT BLACK POWDER COAT #10-7011.
3. USP2MK-C6B KIT CONTAINS:
 (2) CAT-6 KEYSTONE 110-RJ45 JACK
 (1) UNIVERSAL SUB PANEL
 (4) 6-32 SCREWS

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D. CASTRO CHECKED BY M. MARTINEZ APPROVED BY M. MARTINEZ	DATE 8/1/11 8/1/11 8/1/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845				
	CATEGORY PANELS			PRODUCT DESCRIPTION SUB PNL C6 RJ45/110 2PORT BLK			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. USP2MK-C6B
	SCALE: NONE			CAD FILE: USP2MK-C6B.SLDDRW	SHEET 1 OF 1		