


REVISION		DESCRIPTION	DATE	CHANGED BY	APPROVED
ZONE	REV	ECO-14374	03/27/2025	TDUFRENE	DREBECK



NOTES:

1. RATING:
15A MAX / 250V~ (USA) 125V~ / 250V~ (JAPAN)
10A Max / 250V~ (EUROPE & AUSTRALIA)
2. CABLE SIZE:
3C x 0.75 ~ 1.50mm² MAX
3C x 14~18 AWG
3. CERTIFICATIONS:
KEMA-KEUR / UL / CSA / SAA / AS/NZS / JET
4. ALL DIMENSIONS AND MARKINGS ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
XX = ±.02 [0.5] ± 1/32
XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = ±1 [25] / -0
>12 [305] ≤ 60 [1524] = ±2 [51] / -0
>60 [1524] ≤ 120 [3048] = ±4 [102] / -0
>120 [3048] ≤ 300 [7620] = ±6 [152] / -0
>300 [7620] = ±5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE SHEET
NONE 1 OF 1

DESCRIPTION C13 LOCKING CONNECTOR, DOWN ANGLE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	HBAKKE	ACPWRC-C13LU	C