





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISI

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/20/21	PHOSPODAR




REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]
OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5\%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:

FIBER OPTIC Fiber Optic Economy Coupler, St. simplex single mode, zinc alloy body, ceramic sleeve,
 $XX = \pm .02$ [5] $\pm .732$
 $XXX = \pm .005$ [13] ANGLES $\pm 1^\circ$

THIRD-ANGLE PROJECTION



APPROVALS

DRAWN BY

CHECKED BY

APPROVED BY

DATE

08/12/2021

08/20/2021

08/20/2021

CATEGORY

L-COM
an INFINIT[®] brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

FIBER OPTICS

PRODUCT DESCRIPTION

SIMPLEX SMF, ZINC ALLOY BODY CERAMIC SLEEVE

SIZE

A

43321

ITEM NO.

FOA-STSM1-MC00

REV.
A

SCALE:

NONE

CAD FILE: foa-stsm1-mc00.SLDDRW

SHEET 1 OF 1