




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION

| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
|------|-----|-------------|------------|------------|----------|
| | B | ECO-12741 | 05/05/2023 | DZINN | WDIBELLA |



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. ZINC PLATING THICKNESS $\geq 6 \mu\text{m}$.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:

≤ 12 [305] $= +1$ [25] / -0
 > 12 [305] ≤ 60 [1524] $= +2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] $= +4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] $= +6$ [152] / -0
 > 300 [7620] $= +5\% / -0$

ALL OTHER DIMENSIONAL TOLERANCES:

$.X = \pm .2$ [5] FRACTIONS
 $.XX = \pm .02$ [5] $\pm 1/32$
 $.XXX = \pm .005$ [1.3] ANGLES $\pm 1^\circ$

THIRD-ANGLE PROJECTION



APPROVALS

DATE

L-COM
an INFINIT brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

RACK ACCESSORIES

PRODUCT DESCRIPTION

CABINET & FLOOR STAND - 22 INCH (550mm) 2PK

SIZE

A

CAGE CODE

43321

ITEM NO.

LC-EFS500

REV.

B

SCALE:

NONE

CAD FILE:

LC-EFS500.SLDDRW

SHEET 1 OF 1