





ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	10/23/2024	DMAY	DGUTTADAURO



PIN ASSIGNMENTS
FRONT VIEW

NOTES:

- [QC]** IMPORTANT DIMENSION.
- WATERPROOF RATE: IP67, MATED
- CONNECTOR:
 - HOUSING: THERMOPLASTIC, BLACK
 - PIN: COPPER ALLOY, GOLD PLATED
 - EXTENSION NUT: THERMOPLASTIC, BLACK
 - O-RING: RUBBER, GRAY
 - NUT: METAL
- CLAMP RING: THERMOPLASTIC, BLACK
- SEALING NUT: THERMOPLASTIC, BLACK
- SEAL: RUBBER, GRAY, OD: $\phi 4\text{mm} \sim \phi 7\text{mm}$
- ONE SET UNASSEMBLED IN ONE PE BAG
- TEMPERATURE RANGE: -40°C TO $+105^\circ\text{C}$
- OPERATING VOLTAGE: 60V
- NOMINAL CURRENT: 4A

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 $X = \pm .2$ [5] FRACTIONS
 $XX = \pm .02$ [0.5] $\pm 1/32$
 $XXX = \pm .005$ [0.13] ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 ≤ 12 [305] = ± 1 [25] / -0
 > 12 [305] ≤ 60 [1524] = ± 2 [51] / -0
 > 60 [1524] ≤ 120 [3048] = ± 4 [102] / -0
 > 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0
 > 300 [7620] = $\pm 5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5
SCALE SHEET
NONE 1 OF 1

DESCRIPTION
M12 SENSOR 5 PIN B-CODE RIGHT ANGLE MALE FIELD
TERMINATION CONNECTOR, IP67, FITS 18-26AWG AND 4-7mm
CABLE, 60V, 4A, SCREW-IN STYLE, BLACK

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	M12FT5BM90	A