




ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	11/06/2024	DMAY	DGUTTADAURO



## NOTES:

- QC** IMPORTANT DIMENSION.
- WATERPROOF RATE: IP67, MATED
- CONNECTOR:
  - HOUSING: THERMOPLASTIC, BLACK
  - PIN: COPPER ALLOY, GOLD PLATED
  - EXTENSION NUT: THERMOPLASTIC, BLACK
  - O-RING: RUBBER, GRAY
  - NUT: THERMOPLASTIC, BLACK
- CLAMP RING: THERMOPLASTIC, BLACK
- SEALING NUT: THERMOPLASTIC, BLACK
- SEAL: RUBBER, GRAY, OD:  $\phi$ 8mm~ $\phi$ 10mm
- ONE SET UNASSEMBLED IN ONE PE BAG
- TEMPERATURE RANGE: -40°C TO +105°C
- OPERATING VOLTAGE: 60V
- NOMINAL CURRENT: 12A

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
 $X = \pm .2$  [5] FRACTIONS  
 $XX = \pm .02$  [0.5]  $\pm 1/32$   
 $XXX = \pm .005$  [0.13] ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\leq 12$  [305] =  $\pm 1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $\pm 2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $\pm 4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $\pm 6$  [152] / -0  
 $> 300$  [7620] =  $\pm 5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE<sup>®</sup> brand  
Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5  
SCALE SHEET  
NONE 1 OF 1

DESCRIPTION  
M12 DC POWER 4 PIN T-CODE FEMALE FIELD TERMINATION  
CONNECTOR, IP67, PLASTIC NUT, FITS 16-20AWG AND 8-10mm  
CABLE, 60V, 12A, SCREW-IN, BLACK

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	M12PFT4TF	A