




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |            |            |
|-----------|-----------------|------------|------------|
| REV       | DESCRIPTION     | DATE       | APPROVED   |
| A         | INITIAL RELEASE | 11/29/2022 | Guttadauro |
|           |                 |            |            |
|           |                 |            |            |



P1  
USB TYPE C  
MALE CONNECTOR  
NICKEL PLATED





P2  
USB TYPE C  
MALE CONNECTOR  
NICKEL PLATED  
WITH INTERNAL  
I.C. CHIP

| WIRING MAP             |                        |
|------------------------|------------------------|
| P1                     | P2                     |
| A2                     | B11                    |
| A3                     | B10                    |
| B11                    | A2                     |
| B10                    | A3                     |
| A10                    | B3                     |
| A11                    | B2                     |
| B3                     | A10                    |
| B2                     | A11                    |
| A5                     | A5                     |
| B5                     | B5                     |
| B8                     | A8                     |
| A8                     | B8                     |
| A6                     | A6                     |
| A7                     | A7                     |
| A1, B1, A12, B12 SHELL | A1, B1, A12, B12 SHELL |
| A4, B4, A9, B9         | A4, B4, A9, B9         |

4 PAIR 32AWG INDIVIDUALLY SHIELDED TINNED COPPER WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE  
 1 PAIR 32AWG STRANDED TINNED COPPER  
 4 CONDUCTOR 32AWG STRANDED TINNED COPPER  
 1 CONDUCTOR 23AWG STRANDED TINNED COPPER  
 OVERALL ALUM/POLY FOIL SHIELD, OVERALL BRAID SHIELD PLUS 2 TINNED COPPER DRAIN WIRES  
 JACKET: BLACK PVC WITH BLACK NYLON BRAID

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - PASS 100W (20V5A) 40G 4K@60Hz 5K@60Hz 8K@60Hz TEST.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

|  |   |                            |  |
|--|---|----------------------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  | APPROVALS   | DATE                       | <br>50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |
|  | OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0 | DRAWN BY<br>DFRISIELLO     |  |
| ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]   FRACTIONS ± 1/32<br>.XX = ± .02 [.5]   ANGLES ± 1°<br>.XXX = ± .005 [1.3] | CHECKED BY<br>RCARLESCO   | 11/29/2022                 | CATEGORY<br>USB  |
|  | APPROVED BY<br>Guttadauro   | 11/29/2022                 |  |
| THIRD-ANGLE PROJECTION<br>                | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  | COLOR VARIATIONS MAY OCCUR | SIZE<br><b>A</b>   |
| SCALE: NONE  |   | CAGE CODE<br><b>43321</b>  | ITEM NO.<br>CAU4CC-40M-1M  |
| SHEET 1 OF 1   |   | REV.<br><b>A</b>           |  |