



NOTES:

1. VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 2000V/1 SECOND
CONDUCTOR RESISTANCE: $\leq 22.4 \Omega/1000$ METERS
VOLTAGE RATING: AC 300/500V
2. CABLE MARKING:
CCC A133679 60227 IEC 53 (RVV) 300/500V 3x0.75MM².
3. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
4. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.
5. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm].

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5\%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:
 $.X = \pm .2$ [5] FRACTIONS
 $.XX = \pm .02$ [5] $\pm 1/32$
 $.XXX = \pm .005$ [1.3] ANGLES $\pm 1^\circ$



APPROVALS

DRAWN BY
AKRESOWSK

04/25/2022

CHECKED BY
DGUST

04/25/2022

APPROVED BY
GUTTADAURO

04/25/2022

DATE

L-comTM
an INFINIT[®] brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

POWER PRODUCTS

PRODUCT DESCRIPTION
CABLE ASSY, INTL PWR, TYPE I TO C13R,
10A, 2M

SIZE CAGE CODE ITEM NO.

A **43321** **CPCIC13R-10A-2M**

REV. **A**

SCALE: NONE CAD FILE: CPCIC13R-10A-2M.SLDDRW

SHEET 1 OF 1