


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/17/06	MCCORMICK
B	ECN 5567: NEW FORMAT, ADDED ROHS STAMP AND PACKAGING NOTE	6/27/11	D.FRISIELLO



2X Ø.09 [2.3] THRU

MODEL #	SPLIT SLEEVE MATERIAL	FIBER TYPE
FOA-560	BRONZE	MULTIMODE
FOA-570	ZIRCONIA	SINGLEMODE

RoHS Compliant ✓

NOTES:

MATERIAL:
 HOUSING: PEI (POLYETHERIMIDE)
 SPLIT SLEEVE: SEE TABLE
 DUST CAPS (NOT SHOWN): POLYPROPYLENE

MISCELLANEOUS:
 COUPLERS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RECOMMENDED PANEL THICKNESS: .067 [1.70]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005	APPROVALS DRAWN BY C.MCCORMICK	DATE 10/17/2006	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY R.EVANS	DATE 10/17/2006	
APPROVED BY J.ROBERTS	DATE 10/17/2006	PRODUCT DESCRIPTION LC QUAD ADAPTER	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SCALE: NONE CAD FILE: FOA-560.SLDDRW
SIZE A	FSCM NO. 43321	DWG. NO. FOA-560	REV. B
SHEET 1 OF 1			SHEET 1 OF 1