


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	A	D.GRIFFIN
B	ECN 8625 REMOVE REGULATORY COMPLIANCE NOTE ON DRAWING	01/30/17	J.LABOY

MODEL# HG2405MGUR-	
SUFFIX	CONNECTOR TYPE
NF	N-FEMALE
NM	N-MALE
RSP	RP SMA-PLUG
RTP	RP TNC-PLUG
SM	SMA MALE



NOTES:
PACKAGING:
 COMPONENT SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPEC PKG-00012
 - ALL DIMENSIONS FOR REFERENCE ONLY -

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY B.PUCHASKI	02/04/15		CATEGORY	ANTENNA	
	CHECKED BY K.BURGNER	02/04/15		PRODUCT DESCRIPTION	2.4GHz 5dBi MAGMOUNT OMNI ANTENNA W/10 FOOT PIGTAIL AND CONNECTOR	
APPROVED BY P.PESA	02/04/15	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	FSCM NO. 43321	DWG. NO. HG2405MGUR	REV. B
PROJECTION	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: HG2405MGUR.SLDDRW	SHEET 1 OF 1		