


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |          |           |
|-----------|-----------------|----------|-----------|
| REV       | DESCRIPTION     | DATE     | APPROVED  |
| A         | INITIAL RELEASE | 02/18/15 | D.GRIFFIN |
|           |                 |          |           |
|           |                 |          |           |



| MODEL# HG2408MGUR- |                            |
|--------------------|----------------------------|
| NF                 | N-FEMALE                   |
| NM                 | N-MALE                     |
| RSP                | RP SMA-PLUG                |
| RSJ                | RP SMA-JACK                |
| RTP                | RP TNC-PLUG                |
| RTJ                | RP TNC-JACK                |
| RNP                | RP N-PLUG                  |
| RNJ                | RP N-JACK                  |
| SM                 | SMA MALE                   |
| SF                 | SMA FEMALE                 |
| TM                 | TNC MALE                   |
| TF                 | TNC FEMALE                 |
| BM                 | BNC MALE                   |
| RBP                | RP BNC PLUG                |
| RBJ                | RP BNC JACK                |
| WM                 | WAVE RIDER COMPATIBLE TYPE |
| AM                 | ORINOCO COMPATIBLE TYPE    |
| QP                 | QMA PLUG RIGHT ANGLE       |

**NOTES:**  
 PACKAGING:  
 EACH COMPONENT SHALL BE INDIVIDUALLY PACKAGED  
 IN ACCORDANCE WITH L-COM SPECIFICATION PKG-00012

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

|  |  |                         |  |  |
|--|--|-------------------------|--|--|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm] | APPROVALS  | DATE                    |  | 45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845                             |
|  | DRAWN BY<br>B.PUCHASKI   | 02/18/15                |  | CATEGORY<br><b>ANTENNA</b>   |
|  | DIMENSIONAL TOLERANCES:<br>.X = ±.1 [2.54]<br>.XX = ±.01 [.25]<br>.XXX = ±.005 [.13] | CHECKED BY<br>K.BURGNER | 02/18/15   |  |
| ANGULAR TOLERANCES:<br>ALL = ± 1°                            | APPROVED BY<br>P.PESA  | 02/18/15                | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY | SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. <b>HG2408MGUR</b> REV. <b>A</b> |
| PROJECTION<br>   | COLOR VARIATIONS<br>MAY OCCUR  | SCALE: NONE             | CAD FILE: HG2408MGUR.SLDDRW                                    | SHEET 1 OF 1   |