


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/4/16	D.GRIFFIN



**NOTES:**  
 PACKAGING:  
 COMPONENT SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPEC PKG-00108.  
 -ALL DIMENSIONS FOR REFERENCE-  
**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(ROHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 [2.54] .XX = ±.01 [.25] .XXX = ±.005 [.13]  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS B.PUCHASKI	DATE 12/31/15			45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CHECKED BY P.PESA	12/31/15	CATEGORY <b>ANTENNA</b>		PRODUCT DESCRIPTION 700-2700MHz 8dBi CROSS POLARITY WALL MOUNT PANEL ANTENNA,PIM RATED, W/NF CONNECTORS		
	APPROVED BY P.PESA	12/31/15	SIZE <b>A</b>			FSCM NO. <b>43321</b>	DWG. NO. <b>HG72708XWPPR-NF</b>
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: HG72708XWPPR-NF.SLDDRW	SHEET 1 OF 1

