


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/09/2012	D.GRIFFIN
B	ENC7726 UPDATE PER VENDOR SPECS	01/06/2015	BPUCHASKI
C	ECN 9894: REVISE MODEL TO NEW RELEASE, REMOVE ROHS, PS TO 0031	06/27/2019	MMILLER
D	ECN 11150: ADD TS9 MALE PLUG CONNECTOR TO CHART	05/21/2021	KHIETPAS



MODEL# RE1903U-	
SUFFIX	CONNECTOR TYPE
NF	N-FEMALE
NM	N-MALE
NMR	N-MALE RIGHT ANGLE
RSP	RP SMA-PLUG
RSPR	RP SMA-PLUG RIGHT ANGLE
RTP	RP TNC-PLUG
RNJ	RP N-JACK
RNP	RP N-PLUG
RTPR	RP TNC-PLUG RIGHT ANGLE
SM	SMA MALE
SMR	SMA MALE RIGHT ANGLE
TM	TNC MALE
UM	UHF-MALE
BM	BNC MALE
RBP	RP BNC PLUG
MC	MC CARD MALE
MM	MMCX MALE
TS	TS9 MALE PLUG

SEE CHART FOR CONNECTOR TYPE

NOTES:
 PACKAGING:
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 ALL DIMENSIONS ARE FOR REFERENCE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY BPUCHASKI CHECKED BY P.PESA APPROVED BY P.PESA	DATE 02/08/2012 02/08/2012 02/08/2012	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION ANTOMNI 800-2100MHz 3dbi MAG MNT	SIZE A CAGE CODE 43321 ITEM NO. RE1903U
		SCALE: NONE CAD FILE: RE1903U.SLDDRW	SHEET 1 OF 1