




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	01/19/2020	GUTTADAURO



- NOTES:**
- INGRESS PROTECTION RATING IS IP67 (J1 ONLY, MATED)
  - CONNECTOR CONTACTS HAVE 30 μINCHES GOLD PLATING OVER NICKEL PLATING
  - THE CABLE SHIELD DRAIN WIRE IS CONNECTED TO THE METAL SHELL OF THE JACK
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
  - CABLE ASSEMBLY MUST MEET USB 3.0 REQUIREMENTS
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

PART NUMBER	LENGTH	
	METER	FEET
U3A00021-05M	0.5	1.64
U3A00021-1M	1.0	3.28
U3A00021-105M	1.5	4.92

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY DCUI CHECKED BY SPAN APPROVED BY GUTTADAURO	DATE 01/19/2020 01/19/2020 01/19/2020	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	PRODUCT DESCRIPTION <b>CA, USB 3.0 AM TO WP TYPE AF, SHLD</b>			CATEGORY <b>USB 3.0</b>
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b> CAGE CODE <b>43321</b> DWG. NO. <b>U3A00021</b>
	SCALE: NONE CAD FILE: U3A00021.SLDDRW		SHEET 1 OF 1	REV. <b>A</b>