

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/14/2022	DGUTTADAURO







TABLE B	
LENGTH	CABLE
1FT	24AWG(27/0.10TC)*2C+30AWG(10/0.10TC)*3C, JACKET: PVC WITH GREY COTTON BRAID
3FT	24AWG(27/0.10TC)*2C+30AWG(10/0.10TC)*3C, JACKET: PVC WITH GREY COTTON BRAID
6FT	22AWG(45/0.10TC)*2C+30AWG(10/0.10TC)*3C, JACKET: PVC WITH GREY COTTON BRAID
10FT	22AWG(45/0.10TC)*2C+30AWG(10/0.10TC)*3C, JACKET: PVC WITH GREY COTTON BRAID



PART NUMBER	LENGTH	
	FEET	METERS
USBC2-MM-1FT	1.0	0.30 ±.01
USBC2-MM-3FT	3.0	0.91 ±.01
USBC2-MM-6FT	6.0	1.83 ±.03
USBC2-MM-10FT	10.0	3.05 ±.03

- NOTES:
- CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	6/21/2022	
THIRD-ANGLE PROJECTION 	CHECKED BY HBAKKE	7/13/2022	PRODUCT DESCRIPTION USB2.0 C MALE TO C MALE CABLE ALUMINUM SHELL WITH COTTON BRAID
	APPROVED BY DGUTTADAURO	7/14/2022	SCALE: NONE CAD FILE: USBC2-MM.SLDDRW SHEET 1 OF 1
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE: A CAGE CODE: 43321 ITEM NO.: USBC2-MM REV.: A
	COLOR VARIATIONS MAY OCCUR		