

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/14/2022	DGUITADAURO







TABLE B	
LENGTH	CABLE
1FT	24AWG(27/0.10TC)*2C+30AWG(10/0.10TC)*2C, JACKET: PVC WITH GREY COTTON BRAID
3FT	
6FT	22AWG(45/0.10TC)*2C+30AWG(10/0.10TC)*2C, JACKET: PVC WITH GREY COTTON BRAID
10FT	



PART NUMBER	LENGTH	
	FEET	METERS
USBCA2-MM-1FT	1.0	0.30 ±.01
USBCA2-MM-3FT	3.0	0.91 ±.01
USBCA2-MM-6FT	6.0	1.83 ±.03
USBCA2-MM-10FT	10.0	3.05 ±.03

- NOTES:
1. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	6/21/2022	
THIRD-ANGLE PROJECTION 	CHECKED BY HBAKKE	7/13/2022	PRODUCT DESCRIPTION USB2.0 A MALE TO C MALE CABLE ALUMINUM SHELL WITH COTTON BRAID
	APPROVED BY DGUITADAURO	7/14/2022	SIZE A
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CAGE CODE 43321
	COLOR VARIATIONS MAY OCCUR		ITEM NO. USBCA2-MM
			SCALE: NONE CAD FILE: USBCA2-MM.SLDDRW
			REV. A
			SHEET 1 OF 1