



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/29/2022	DGUITADAURO



PART NUMBER	LENGTH	
	FEET	METERS
USBCHDMI-MM-F-1M	3.28	1.0 ±.03

- NOTES:
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	08/09/2022	
OVERALL CABLE LENGTH TOLERANCE:	CHECKED BY HBAKKE	8/29/2022	CATEGORY
≤12 [305] = +1 [25] / -0	APPROVED BY DGUITADAURO	8/29/2022	AUDIO/VIDEO
>12 [305] ≤60 [1524] = +2 [51] / -0	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION
>60 [1524] ≤120 [3048] = +4 [102] / -0	THIRD-ANGLE PROJECTION		USB C TO HDMI 2.0 MALE TO MALE
>120 [3048] ≤300 [7620] = +6 [152] / -0	COLOR VARIATIONS MAY OCCUR	SIZE A	W/ FERRITES, 4K, NYLON BRAIDED CABLE
>300 [7620] = +5% / -0	SCALE: NONE	CAGE CODE 43321	ITEM NO. USBCHDMI-MM-F
ALL OTHER DIMENSIONAL TOLERANCES:	SCALE: NONE	CAD FILE: USBCHDMI-MM-F.SLDDRW	REV. A
.X = ±.2 [5] FRACTIONS ± 1/32	SHEET 1 OF 1		
.XX = ±.02 [5] ANGLES ± 1°			
.XXX = ±.005 [13]			