

DC and AC-EC Fans



L-com fans are designed to improve the air flow in your cabinet or rack. Our fans help protect equipment from overheating; therefore, eliminating performance issues and extending your equipments life span.

Model/SKU Number	LCFAN100240VULEC	LC1UFNSH4ECUL	LC1UFNSH2ECUL	LC1UFNSH2ECUL110VTC	LC1UFNSH4ECUL110VTC	LC3UFNSH3ECUL110V					
PHYSICAL											
Rack Capacity (in Rack Units)	N/A	1U	1U	1U	1U	3U					
Number of Fans	1	4	2	2	4	3					
Unit Dimensions (in)	H	4.7	1.75	1.75	1.75	5.25					
	W	4.7	19	19	19	19					
	D	1.5	13	6.69	6.69	1.57					
CFM	99.42	397.68	198.84	198.84	397.68	298.26					
Input Voltage	110V 50/60Hz (AC/EC)	110V 50/60Hz (AC/EC)	110V 50/60Hz (AC/EC)	110V 50/60Hz (AC/EC)	110V 50/60Hz (AC/EC)	110V 50/60Hz (AC/EC)					
Switches	N/A	Lighted ON/OFF Rocker Switch									
Painting/ Coating	Electro-static Powder Coating - Black										
Construction	Cold Rolled Steel										
Color	Black										
ADDITIONAL FEATURES											
Noise Level	~42.3dBA (AC/EC)										
Temperature Control	N/A	N/A	N/A	Intelligent Control Digital Temperature Thermostat	Intelligent Control Digital Temperature Thermostat	N/A					
Assembly	No Assembly Required										
COMPATIBLE											
EIA/ECA-310-E	N/A	✓									
SHIPPING											
Shipping Dimensions (in)	L	7	21	21	21	20					
	W	6	16	10	16	8					
	H	2	2.4	2.4	2.4	4					
Shipping Weight (lbs.)	1.15	13.9	7.4	7.75	14.2	9					

DC and AC-EC Fans

Model/SKU Number	LCFAN12VDCVUL	LC1UFNSH4UL12DC	LC1UFNSH2UL12DC	LC1UFNSH2TCUL12DC	LC1UFNSH4ULTC12DC	LC3UFNSH3UL12DC					
PHYSICAL											
Rack Capacity (in Rack Units)	N/A	1U	1U	1U	1U	3U					
Number of Fans	1	4	2	2	4	3					
Unit Dimensions (in)	H	4.7	1.75	1.75	1.75	5.25					
	W	4.7	19	19	19	19					
	D	1.5	13	6.69	6.69	1.57					
CFM	130.45	521.8	260.9	260.9	521.8	391.35					
Input Voltage	12VDC	110V power adapter to 12VDC (DC)	110V power adapter to 12VDC (DC)	110V power adapter to 12VDC (DC)	110V power adapter to 12VDC (DC)	110V power adapter to 12VDC (DC)					
Switches	N/A	Lighted ON/OFF Rocker Switch									
Painting/ Coating	Electro-static Powder Coating - Black										
Construction	Cold Rolled Steel										
Color	Black										
ADDITIONAL FEATURES											
Noise Level	~46.13dBA (12VDC)										
Temperature Control	N/A	N/A	N/A	Intelligent Control Digital Temperature Thermostat	Intelligent Control Digital Temperature Thermostat	N/A					
Assembly	No Assembly Required										
COMPATIBLE											
EIA/ECA-310-E	N/A	✓									
UL listed Fans	✓										
SHIPPING											
Shipping Dimensions (in)	L	7	21	21	21	21					
	W	6	16	10	10	16					
	H	2	2.4	2.4	2.4	2.4					
Shipping Weight (lbs.)	1.15	13.9	7.4	7.75	14.2	9					