

1U Rack mount (2 UL listed) Fan with temp. control, 110v, with NEMA 5-15P (US) Plug, Cord Length 2M



LC-2FRM1UTC-110V

Features

- Lighted ON/OFF Rocker Switch
- Quiet function
- Easy rack-mounting to standard 19" racks and cabinets
- 2 fans in an efficient 1U space
- Front Temperature Control Digital Thermostat

Applications

- 19 Inch Cabinet

Description

The L-com LC-2FRM1UTC-110V 1U fan unit with 2 UL listed fans conveniently mounts on standard 19-inch racks and cabinets to increase air flow, helping to prevent overheating and enhancing equipment performance. This fan unit operates quietly, with a maximum noise level of 43db-A to 47db-A. Our 1U fan unit is constructed of high-quality steel with a powder-coated finish.

Our fan unit comes with a NEMA 5-15P plug and a 2-meter cord. Even inside an equipment filled rack or cabinet, the lighted on/off rocker switch is easy to see and operate. This EIA/ECA compliant 1U fan unit comes fully assembled for a quick and easy installation. The L-com LC-2FRM1UTC-110V fan panel has dimensions of 6.69 inches L x 19 inches W x 1.75 inches H and requires an input voltage of 110 volts at 50/60Hz.

L-com has one of the largest in-stock selections of 1U fan units with 2 UL-listed fans, with same-day shipment for domestic and international orders. Make your online purchase right now to take advantage of our same-day shipping. Our expert technical support and knowledgeable sales team can assist you in obtaining the 1U fan unit that meets your needs.

Configuration

Enclosure Color	Black
Number of Fans	2
Mount Option	Rack Mount

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Voltage		110		VAC
RPM		2650/3000		

Mechanical Specifications

Size		
Length	6.69 in	[169.93 mm]
Width	19 in	[482.6 mm]
Height	1.75 in	[44.45 mm]
Weight	7.75 lbs	[3.52 kg]

1U Rack mount (2 UL listed) Fan with temp. control, 110v, with NEMA 5-15P (US) Plug, Cord Length 2M



LC-2FRM1UTC-110V

1U Rack mount (2 UL listed) Fan with temp. control, 110v, with NEMA 5-15P (US) Plug, Cord Length 2M from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/1u-rack-mount-2-ul-listed-fan-temp-control-110v-nema-5-15p-us-plug-cord-2m-lc-2frm1utc-110v-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

1U Rack mount (2 UL listed) Fan with temp. control, 110v, with NEMA 5-15P (US) Plug, Cord Length 2M CAD Drawing

1U Rack mount (2 UL listed) Fan with temp. control, 110v, with NEMA 5-15P (US) Plug, Cord Length 2M

