

42U Cabinets



Model / SKU Number	LC42USRC800PDCM	LC42USRC800GDCM	LC42USRC800PDFRFC	LC42USRC800GDFRFC	LC42USRC800PDCM-W	LC42USRC800GDCM-W	LC42USRC800PDFRFC-W	LC42USRC800GDFRFC-W	LC42USRC1000PDFRFC	LC42USRC1000PDFRCM	LC42USRC1000GDFRFC	LC42USRC1000GDFRCM	LC42USRC1000PDFRFC-W	LC42USRC1000PDFRCM-W	LC42USRC1000GDFRFC-W	LC42USRC1000GDFRCM-W	LC42USRC1200PDFRCM	LC42USRC1200PDFRFC	LC42USRC1200GDFRCM	LC42USRC1200GDFRFC	LC42USRC1200PDFRCM-W	LC42USRC1200PDFRFC-W	LC42USRC1200GDFRCM-W	LC42USRC1200GDFRFC-W
Physical	42U x 600 mm x 800 mm								42U x 600 mm x 1,000 mm								42U x 600 mm x 1,200 mm							
Features																								
Front Door Type: Perforated	✓		✓		✓		✓		✓	✓			✓	✓			✓	✓			✓	✓		
Front Door Type: Glass		✓		✓		✓		✓			✓	✓			✓	✓			✓	✓			✓	✓
Top Design: Fan			✓	✓			✓	✓	✓		✓		✓		✓	✓			✓	✓			✓	✓
Top Design: Cable Management	✓	✓			✓	✓				✓		✓		✓	✓		✓	✓		✓	✓		✓	✓
DIMENSIONS & SPECIFICATIONS																								
Static Weight Capacity (lbs / kg)	3000 / 1350								3000 / 1350								3000 / 1350							
Weight Capacity on Casters (lbs / kg)	2400 / 1088								2400 / 1088								2400 / 1088							
External Height (mm)	2000.4								2000.4								2000.4							
External Width (mm)	600								600								600							
D1 External Depth (mm)	893								1093								1293							
D2 Distance Between Levelers (mm)	571								571								571							
D3 Distance Between Levelers (mm)	823.2								1023.2								1223.2							
D4 (mm)	555								755								955							
D5 (mm)	680								880								1080							
D6 (mm)	878								878								876							
D7 (mm)	1110								1310								1510							
D8 (mm)	1378								1578								1778							
D9 9mm	1644								1844								2044							
D10 (mm)	890								890								890							

