

## Mid Depth Cabinets



**L-Com's Mid Depth Cabinets are perfect for storing your rack mountable servers, networking, and telecommunications equipment. Perforated ventilation and pre-cut fan slots for user supplied fans help keep your equipment cool.**

Model / SKU Number		LCSMT6812B	LCSMT6818B	LCSMT6824B
PHYSICAL				
Rack Capacity (in Rack Units)		12U	18U	24U
Depth		838mm	838mm	838mm
Unit Dimensions (in)	H	28.5	39	49
	W	23.65	23.65	23.65
	D	33	33	33
Maximum Rail Depth (in)		30	30	30
Weight Capacity (kg / lbs)		454 / 1000	454 / 1000	454 / 1000
Material		Cold Rolled Steel		
Painting / Coating		Black Powder Coating		
Door Type		Perforated Door		
Rack Hole Type		Square Holes		
ADDITIONAL FEATURE				
Casters		Casters Included. Casters Add 3" to External Height		
Leveling Feet		4 Adjustable Leveling Feet Included		
Cable Management		Top and Bottom Covers Screw On and Off (Replaceable)		
Security		Locks Included for Door, Back, and Side Panels		
Cooling		Vented door and side panels for peak efficiency of airflow. Option for mounting two fans on top panel		
Shelving		One Set of "L" Brackets Included		
Assembly		Assembled		
COMPLIANCE AND CERTIFICATIONS				
EIA/ECA310-E		✓	✓	✓
ROHS		✓	✓	✓
CE		✓	✓	✓
PCI		✓	✓	✓
HIPAA		✓	✓	✓
NEMA Rated Type-1		✓	✓	✓
IP20 Protection Grade		✓	✓	✓
SHIPPING				
Shipping Dimensions (in)	L	35	35	35
	W	25	25	25
	H	34	44	54
Shipping Weight (lbs)		93	106	122

## Mid Depth Cabinets

