

## 14x12x6 Inch Weatherproof Industrial Enclosure with Corner Screws and Blank Non-Metallic Mounting Plate - Model: NBC141206-KIT01

### Applications

- Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Industrial control equipment installations
- High temperature or corrosive environments
- Hydraulic or pneumatic control installations

### Features

- Rugged FRP Material with gasketed lid
- Stainless steel cover screws
- Excellent temperature range
- UL/CSA/NEMA/IP rated
- Includes blank Non-Metallic Starboard mounting plate



### Description

The NBC series is a UL/CSA® Listed rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The integral mounting flange allows it to be wall mounted as well as on a flat surface without the need for extra mounting hardware. The fully gasketed lid features four stainless steel captive screws that secure the cover to the base by means of four threaded brass inserts contained in the base that provide a weather-proof seal protecting the contents inside. The light grey color of the NBC series is cleaner, cooler and more aesthetically pleasing. Users can enjoy the physical benefits of better heat reflection and better UV resistance due to the lighter color. The contoured body provides an attractive and contemporary appearance.


The NBC series is ideal for custom applications, which may require special modifications to the enclosure. Contact L-com with your custom requirements and let us provide it for you. Integral mounting stand-offs inside the enclosure can be used for mounting plates.

The NBC141206-KIT01 includes a Blank Non-Metallic Starboard Mounting Plate permitting free form layout of equipment. The Enclosure and Mounting Plate combination is ideal for custom applications. Mounting stand-offs inside the enclosure are used to secure the Mounting Plate.

Mushroom Head Cover



Ribbed Cover Corners



Molded Mounting Flanges



**Specifications**

**Enclosure Specifications**

<b>Enclosure Material</b>	Halogen free, self extinguishing fiberglass reinforced polyester (FRP)
<b>Enclosure Color</b>	Light Grey (RAL 7036)
<b>Weight</b>	9.7 lbs (4.40 kg)
<b>Outside Dimensions (max)</b>	13.3 x 15.3 x 6.7 in (338 x 389 x 170mm)
<b>Inside Dimensions</b>	12.0 x 14.0 x 5.8 in (305 x 356 x 148mm)
<b>Temperature Ratings</b>	Continuous: -58°F to 302°F (-50°C to 150°C) Momentary exposure up to 392°F (200°C).
<b>UL and CSA Approved</b>	Yes
<b>RoHS Compliant</b>	Yes
<b>NEMA Ratings*</b>	Type 3, 3R, 3S, 4, 4X, 12 and 13
<b>IEC 529 Ratings*</b>	IP66-11

\*Ratings prior to modifications

**Mounting Plate Specifications**

<b>Plate Material</b>	Non-Metallic Starboard
<b>Dimensions</b>	12.75 x 10.85 in. (324 x 276 mm)

