

## 16x14x06" UL FRP NEMA Encl,w/PolyP Blnk Mnt Plt

### NBF161406-KIT01



#### Features

- UL Listed Molded Fiberglass Reinforced Polyester (FRP) industrial enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 4 / IP66 rated
- Fully gasketed lid & integral mounting flange

#### Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid deployment installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage

#### Description

The NBF161406-KIT01 is a UL® Listed rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded halogen free self extinguishing fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The integrated mounting flange allows mounted directly to any flat wall surface provided proper screws are used into secure studs. The fully gasketed lid features a stainless steel continuous hinge and a stainless steel quick release latch with padlock hasp. The enclosure material is UV stabilized and comes in a light gray color.

The 0.25 inch thick blank Non-Metallic marine board mounting plate included with the NBF161406-KIT01 comes uninstalled and kitted with the enclosure so that you can modify and install as needed.

The NBF161406-KIT01 now comes with the UL Listing Mark in every enclosure. Ideal for all construction sites and equipment enclosure applications.

\*Note: Any holes or openings you might introduce must be properly sealed to maintain NEMA Type 4 / IP66 rating

#### Mechanical Specifications

##### Size

Outer Height	17.53 in	[445.26 mm]
Outer Width	15.46 in	[392.68 mm]
Outer Depth	6.21 in	[157.73 mm]
Inner Height	15.6 in	[396.24 mm]
Inner Width	13.6 in	[345.44 mm]
Inner Depth	5.9 in	[149.86 mm]
Weight	12.7 lbs	[5.76 kg]
Enclosure Material	Fiberglass Reinforced Polyester (FRP)	

#### Environmental Specifications

Temperature Continuous	-60 to +134°C
Ingress Protection (IP) Rating	IP66

16x14x06" UL FRP NEMA Encl,w/PolyP Blnk Mnt Plt

**NBF161406-KIT01**



---

### Compliance Certifications

16x14x06" UL FRP NEMA Encl,w/PolyP Blnk Mnt Plt from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/16x14x06-inch-ul-listed-fiberglass-reinf-polyester-frp-weatherproof-outdoor-ip66-nema-4-enclosure-kit-bundled-w-non-metallic-blank-mount-plate-nbf161406-kit01-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

NBF161406-KIT01 CAD Drawing
16x14x06" UL FRP NEMA Encl,w/PolyP Blnk Mnt Plt

