

14x10x04 ABS Plastic Weatherproof Outdoor IP55 NEMA 3 Enclosure, Hook & Loop Mounting, 120 VAC outlets Gray (4-Pack)

NBP141004-100-4



Features

- Compact Weatherproof Molded ABS Enclosure
- Fully gasketed padlockable raised lid
- NEMA Type 3 / IP55 rated
- Removable 120 VAC power module
- Heavy duty hook-and-loop tape for mounting equipment in enclosure

Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage

Description

Secure your wireless equipment...

Remote wireless equipment such as access points, routers and bridges often are more vulnerable to tampering and theft. This can disrupt and even cripple critical communications. A low cost solution for protecting and securing your wireless equipment is the NBP141004-100-4. This rugged, weather-proof composite enclosure is ideal for both indoor and outdoor applications. The compact size of this enclosure makes it ideal for locations with limited space requirements such as equipment closets or mobile applications. Also due to its size, the NBP141004-100-4 can be used where aesthetics are important, such as in offices and in public areas requiring HotSpots.

The 10.5" x 9.5" x 4" (266 x 241 x 101 mm) compartment features a removable power module with two 120 VAC outlets. This power module has provisions to install two additional outlets. Cable access to the inside of the enclosure is via three rubber cable glands located on the bottom. Equipment can be mounted inside the enclosure by using the included hook-and-loop tape. The raised lid features a continuous gasket and a quick release latch with provisions for a padlock. The enclosure material is UV stabilized molded ABS. Three gasketed mounting holes are provided inside the enclosure for easy installations.

The HGX-PMT17 pole mounting kit (sold separately) is specifically designed for this enclosure and allows you to securely mount the enclosure to any 3-12 inch diameter pole

These enclosures are also sold individually as Item #NBP141004-100

Mechanical Specifications

Size

Outer Height	14.5 in	[368.3 mm]
Outer Width	10.6 in	[274.32 mm]
Outer Depth	4.3 in	[109.22 mm]
Inner Height	10.5 in	[266.7 mm]
Inner Width Inner	9.5 in	[241.3 mm]
Depth	4 in	[101.6 mm]
Weight	12 lbs	[5.44 kg]
Enclosure Material	ABS Plastic	

Environmental Specifications

NEMA Rating	3
Ingress Protection (IP) Rating	IP55

14x10x04 ABS Plastic Weatherproof Outdoor
IP55 NEMA 3 Enclosure, Hook & Loop
Mounting, 120 VAC outlets Gray (4-Pack)



NBP141004-100-4

Compliance Certifications

UL Listed

No

14x10x04 ABS Plastic Weatherproof Outdoor IP55 NEMA 3 Enclosure, Hook & Loop Mounting, 120 VAC outlets Gray (4-Pack) from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning

and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/nema-enclosures-14x10x4-inch-120-vac-weatherproof-enclosure-4-pack-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

NBP141004-100-4 CAD Drawing
14x10x04 ABS Plastic Weatherproof Outdoor IP55 NEMA 3 Enclosure,
Hook & Loop Mounting, 120 VAC outlets Gray (4-Pack)

