


14x10x04 ABS Plastic Weatherproof Outdoor IP24 NEMA 3R Enclosure, Hook & Loop Mounting, Fan & 120 VAC outlets Gray

NBP141004-10FW



Features

- Compact Weatherproof Molded ABS Enclosure
- Fully gasketed padlockable raised lid, Vented with Rain Guards and Thermostat controlled Cooling Fan
- NEMA Type 3R / IP24 rated
- Removable 120 VAC power module
- Heavy duty hook-and-loop tape for mounting equipment in enclosure

Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage

Description

Secure your wireless equipment...

Remote wireless equipment such as access points, routers and bridges often are more vulnerable to tampering and theft. This can disrupt and even cripple critical communications. A low cost solution for protecting and securing your wireless equipment is the NBP141004-10FW. This rugged, weather-proof composite enclosure is ideal for both indoor and outdoor applications. The compact size of this enclosure makes it ideal for locations with limited space requirements such as equipment closets or mobile applications. Also due to its size, the NBP141004-10FW can be used where aesthetics are important, such as in offices and in public areas requiring HotSpots.

The 10.5" x 9.5" x 4" (266 x 241 x 101 mm) compartment features a removable power module with two 120 VAC outlets. This power module has provisions to install two additional outlets. Cable access to the inside of the enclosure is via three rubber cable glands located on the bottom. Equipment can be mounted inside the enclosure by using the included hook-and-loop tape. The raised vented lid has rain guards installed to allow for outdoor installations and features a continuous gasket and a quick release latch with provisions for a padlock. The enclosure material is UV stabilized molded ABS. Three gasketed mounting holes are provided inside the enclosure for easy installations.

Cooling:

To help ensure trouble-free operation of electronic equipment, proper operating temperatures inside an enclosure needs to be maintained. With the built-in cooling fan, internal temperatures can be better maintained. This model is ideal in hot environments.

The NBP141004-10FW model includes a thermostat-controlled 6.8W (Max.) fan. The high airflow, low noise fan used allows warm air to be actively pushed out while the lower vent passively pulls in outside air into the enclosure. Filters for both ports prevent foreign objects or debris from entering the enclosure. The fan turns on when the internal temperature rises to 120° F (49° C) ±5° and turns off at 90° F (32° C) ±10°. The cooling fan does not require the use of any of the AC outlets, leaving them all available for your equipment.

The HGX-PMT17 pole mounting kit (sold separately) is specifically designed for this enclosure and allows you to securely mount the enclosure to any 3-12 inch diameter pole


Mechanical Specifications

Size

Outer Height	14.5 in	[368.3 mm]
Outer Width	10.6 in	[274.32 mm]
Outer Depth	4.3 in	[109.22 mm]
Inner Height	10.5 in	[266.7 mm]
Inner Width Inner	9.5 in	[241.3 mm]
Depth	4 in	[101.6 mm]
Weight	3.8 lbs	[1.72 kg]
Enclosure Material	ABS Plastic	

14x10x04 ABS Plastic Weatherproof Outdoor IP24 NEMA 3R Enclosure, Hook & Loop Mounting, Fan & 120 VAC outlets Gray

NBP141004-10FW



Environmental Specifications

NEMA Rating	3R
Ingress Protection (IP) Rating	IP24

Compliance Certifications

UL Listed	No
-----------	----

14x10x04 ABS Plastic Weatherproof Outdoor IP24 NEMA 3R Enclosure, Hook & Loop Mounting, Fan & 120 VAC outlets Gray from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning

and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/nema-enclosures-14x10x4-inch-120-vac-outdoor-weatherproof-enclosure-with-cooling-fan-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

NBP141004-10FW CAD Drawing
14x10x04 ABS Plastic Weatherproof Outdoor IP24 NEMA 3R Enclosure,
Hook & Loop Mounting, Fan & 120 VAC outlets Gray

