


| REVISIONS | | | |
|-----------|--|------------|----------|
| REV. | DESCRIPTION | DATE | APPROVED |
| F | ECN 10574: UPDATE CENTER PIN STRUCTURE | 07/03/2020 | SRAUTUS |


[20.0]







RECOMMENDED PIN CRIMP SIZE



RECOMMENDED CABLE STRIPPING

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

 $.X = \pm .2$ [5.08] FRACTIONS $.XX = \pm .02 [.51]$ ± 1/32 .XXX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0

120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

an INFINIT@ brand

50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA. Phone: 1.800.341.5266 | 1.978.682.6936

Fax: 1.978.689.9484 Website: www.L-com.com E-mail: CustomerService@L-com.com THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY ALL RIGHTS RESERVED.

N/A

SIZE CAGE CODE DRAWN BY ITEM NO. REV 43321 **DPURWIN** F ANM-1700

REGULATORY COMPLIANCE:

EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.