



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|------------------------------|---------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | REPLACES DRAWING CIB24XE-OD1 | 7/14/14 | D. CASTRO |
| . | . | . | . |
| . | . | . | . |
| . | . | . | . |




FEMALE 24-PIN MINIATURE RIBBON CONNECTOR



2X ISO M3.5 X 0.6 SCREWLOCK

FOIL SHIELD

2X ISO M3.5 X 0.6 JACKSCREW





MALE 24-PIN MINIATURE RIBBON CONNECTOR

NOTES:

- WIRED STRAIGHT THROUGH FROM PIN TO LIKE-NUMBERED PIN.
- MATERIALS AND FINISHES:
 CONNECTOR CONTACTS: BRASS, GOLD-PLATED
 INSULATORS: BLUE POLYBUTYLENE TEREPHTHALATE
 CONNECTOR FLANGES AND GUARDS: DIE-CAST ALUMINUM ALLOY, NICKEL-PLATED
 BUSHINGS: BRASS, NICKEL-PLATED
 SHIELD: ADHESIVE COPPER FOIL
 JACKSCREWS: STEEL, BLACK OXIDE FINISH
- CONNECTORS COMPATIBLE WITH ALL L-COM IEEE-488 PRODUCTS AND MOST SIMILAR OTHER 24-PIN MINIATURE RIBBON CONNECTORS.
- SUPPLIED WITH POLYETHYLENE DUST COVERS.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

| | | | | | | |
|---|---|----------------------------|--|--|------------------|--------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE |  45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | | | |
| | DRAWN BY T CLARK | 10/30/01 | | CATEGORY IEEE-488 | | |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3] | CHECKED BY D PARHAM | 10/31/01 | PRODUCT DESCRIPTION IEEE-488 ULTRA SLIMLINE EXTENDER | | | |
| | APPROVED BY C. McCORMICK | 11/1/01 | | <table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 43321</td> <td>DWG. NO. CIB24XE</td> <td>REV. A</td> </tr> </table> | SIZE A | FSCM NO. 43321 |
| SIZE A | FSCM NO. 43321 | DWG. NO. CIB24XE | REV. A | | | |
| PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED DETAILS MAY VARY | | SCALE: NONE | | | |
| COLOR VARIATIONS MAY OCCUR | | CAD FILE: CIB24XE.SLDDRW | SHEET 1 OF 1 | | | |