


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

| REVISIONS | | | |
|-----------|----------------------|-------------|------------|
| REV | DESCRIPTION | DATE | APPROVED |
| C | ECN 4686: CN RELEASE | 13.APR.2010 | Bill_Zhang |
| | | | |
| | | | |



| WIRING CHART | |
|--------------|--------|
| DB 9P M | BNC M |
| PIN1 | P1 |
| PIN2 | P2 |
| PIN3 | P3 |
| PIN4 | P4 |
| PIN5 | N/C |
| PIN6 | SHIELD |
| PIN7 | SHIELD |
| PIN8 | SHIELD |
| PIN9 | SHIELD |
| SHELL | SHIELD |

| PART NUMBER | LENGTH FEET [METERS] |
|-------------|----------------------|
| CTL4CAD-1.5 | 1.5 [.46] |
| CTL4CAD-3 | 3.0 [.91] |
| CTL4CAD-6 | 6.0 [1.82] |

ALL BNC SHIELDS TIED TO SHELL

- NOTES:
1. CABLE SHALL BE TESTED FOR CONTINUITY.
 2. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 3. DB9 CONNECTOR DUST COVER INSTALLED FOR SHIPPING (NOT SHOWN)

| | | | |
|--|--|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | APPROVALS DRAWN BY Bill_Zhang | DATE 03/05-'10 | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | CHECKED BY Frank_Mao | DATE 03/05-'10 | |
| APPROVED BY Thomas_Lu | DATE 03/05-'10 | PRODUCT DESCRIPTION CA VGA BKT DB9 M/4 BNC M | REF |
| PROJECTION | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 |
| REF | SCALE: NONE | DWG. NO. CTL4CAD | CAD FILE: CTL4CAD.SLDDRW |
| REF | SHEET 1 OF 1 | REV. C | SHEET 1 OF 1 |