



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/3/15	D.GRIFFIN
B	ECN 8113: UPDATE STRANDED CONDUCTOR TO SOLID FOR CABLE	10/14/15	S.LI



**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU (RoHS DIRECTIVE)

MODEL NUMBER	LENGTH METERS [FEET]
DPCAC3MM-0.5M	0.5 [1.64]
DPCAC3MM-1M	1.0 [3.28]
DPCAC3MM-2M	2.0 [6.56]
DPCAC3MM-3M	3.0 [9.84]
DPCAC3MM-5M	5.0 [16.41]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY R.SCOTT APPROVED BY S.SMITH	DATE 4/4/14 4/4/14 4/4/14	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY AUDIO/VIDEO PRODUCT DESCRIPTION CA MINI DP M/MINI DP M	
SCALE: NONE		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. DPCAC3MM	REV. <b>B</b>
CAD FILE: DPCAC3MM.SLDDRW			SHEET 1 OF 1		