



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/07/17	J.LABOY



SECTION A-A



NOTES:

- MATERIAL:**
HOUSING: ABS, UL94V-0
FINISH: (FRONT SURFACE AND EDGES) CHARMILLES #27, COLOR, BLACK
- MISCELLANEOUS:**
2x, #4-40 UNC-2A PAN HEAD SCREWS, INCLUDED.
OPERATING TEMPERATURE RANGE: -10° C TO +70° C.
BULK PACKAGE 25 ADAPTERS PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [13]	APPROVALS DRAWN BY D.CUI CHECKED BY S.PAN APPROVED BY D.GUITADAURO	DATE 07/03/17 07/03/17 07/03/17	L-com Global Connectivity 50 HIGH STREET NORTH ANDOVER, MA 01845		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR		
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CPLR PNL MNT BLANK FLAT FRONT	SIZE A	FSCM NO. 43321
	PROJECTION 	ECF-SK	DWG. NO. ECF-BLANK25	REV. A	SCALE: NONE CAD FILE: ECF-BLANK25.SLDDRW SHEET 1 OF 1