
8 <u>1</u> 7 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPER L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRIT PERMISSION OF L-COM, INC. IS PROHIBITED.	RTY OF	3 2 REVISIONS REV DESCRIPTION DATE APPROVED A DRAWING REPLACES MD66FF-OD1 06/23/2014 DCASTRO B ECN 9926; REMOVED PIN MARKING, REMOVED ROHS STATEMENT 06/25/2019 BGATES U
PIN 5	.08	PIN 4 PIN 4 PIN 2 PIN 2 PIN 6 PIN 6 PIN 6 PIN 6 PIN 5 PIN 3 PIN 5 NUT AND WASHER REMOVED FOR CLARITY
В	BODY Ø.43 [11] Ø.43 ([11.86])	<pre>475</pre>
 NOTES: 1. D-FLAT AND RECTANGULAR SLOT ARE PARA SIDE VIEW. 2. PINS ARE WIRED STRAIGHT THROUGH. 3. FINISH: NICKEL PLATED BRIGHT. 4. INTERNAL TOOTH LOCK WASHER AND HEX N 5. ADAPTER SHALL BE TESTED FOR CONTINUITY. 6. ADAPTER SHALL BE INDIVIDUALLY PACKAGE SPECIFICATION PS-0031. 	IUT INCLUDED.	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: \$12 [305] = +1 [25].0 >> 212 [305] = +5%.7.0% PROJECT DESCRIPTION BGATES Date Dersieuto 06/25/2019 Date Dersieuto 06/25/2019 Date Dersieuto 06/25/2019 Date Dersieuto 06/25/2019 06/25/2019 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.0 [51] .XXX = ±.005 [.13] ONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY PROVECT DESCRIPTION BCATES ADPT, MINI-DIN 6 F/F BULKHEAD VARY VARY COLOR VARIATIONS MAY VARY SIZE FSCM NO. B DWG. NO. B MD666FF B 3 2







D

С

В