


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/15/07	D.FRISIELLO




2X, CAT 6 KEYSTONE FEED-THRU COUPLER

NOTES:

1. PANEL MATERIAL: .06 [1.5] THK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. KIT CONTAINS 4, #6-32 UNC SCREWS.

DIMENSIONS ARE IN INCHES [mm]
 UNLESS OTHERWISE SPECIFIED, TOLERANCES TO BE:
 .X ±1 [25] ANGLES ±2°
 .XX ±0.1 [25]
 .XXX ±0.05 [13]
 OVERALL CABLE LENGTH TOL:
 ≤ 60 [1524] +3 [76.2] / - 0
 > 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY D.FRISIELLO	3/15/07
CHECKED BY P.McNEIL	3/15/07
APPROVED BY J.ROBERTS	3/15/07

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY USP SUB PANEL			
PRODUCT DESCRIPTION USP SUB PANEL, W/2 CAT 6 STRAIGHT COUPLERS			
SIZE A	FSCM NO. 43321	DWG. NO. USP2MC6B	REV. A
SCALE: FULL		CAD FILE: USP2MC6B.SLDDRW	SHEET 1 OF 1