

5

## SPECIFICATIONS:

IP RATING: 67 INDUSTRIAL (WHEN MATED)

## MECHANICAL:

А

O-RING: RUBBER (NBR) IP67 ADAPTER AND NUT: HIGH IMPACT FLAME RETARDANT PLASTIC TEMPERATURE: -40°F TO 150°F (-40°C TO +68°C)

7

## MISCELLANEOUS:

8

ALL DIMENSIONS ARE FOR REFERENCE ONLY. COMPONENTS COME UN-ASSEMBLED AND SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

6

											1
	UNLESS OTHERWISE SPECIFIED,	APPROVALS	DATE					50	HIGH STRI	EET	Í
	DIMENSIONS ARE IN INCHES [mm]	DRAWN BY		-		ノし	S	NORTH	ANDOVE	ER, MA	l l
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0	DFRISIELLO	an INFINIT <sup>©</sup> brand 01845							Í	
	>12 [305] \$60 [1524] = +2 [51] / -0	CHECKED BY DGUTTADAUR	11/06/2019	CATEGO	RY						A
	$200 [7(20)] = \pm 67 (00)$	APPROVED BY	11/00/2017	-	TELECOM/MODULAR						´`
		DGUTTADAUR	11/06/2019	TELECOMITIODULAR							l I
	ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$ [5] $.XX = \pm .02$ [.5] $.XXX = \pm .005$ [.13]	CONFIGURATIO UNDIMENSIONE MAY V	PRODUCT DESCRIPTION IP67 RJ45 PLUG KIT COMPATIBLE W/ WP67-BHA-DC							2019	
		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE C 433				A REV.	(OD) mo	
				SCALE: NONE			s		1 OF 1	Ŭ Ŭ	
	<b>↑</b> 4	3		I		2			1		