


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7231: REVISED DESCRIPTION FOR "HOOD", NEW FORMAT, ROHS NOTE	1/9/13	D.FRISIELLO



WIRING MAP		
"J1"	WIRE COLOR	"J2"
1	BLACK	1
2	GRAY	3
3	RED	2
4	GREEN	4
5	BROWN	5
6	BLUE	6
7	ORANGE	7
8	YELLOW	8
9	PURPLE	9
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CSNULL9FF-5	5.0	1.52
CSNULL9FF-10	10.0	3.05
CSNULL9FF-25	25.0	7.62

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY TJC	6/7/01		
	CHECKED BY DFP	7/18/01	PRODUCT DESCRIPTION CABLE, DB9F/DB9F NULL MODEM	
	APPROVED BY CM	7/19/01		SIZE A FSCM NO. 43321 DWG. NO. CSNULL9FF REV. E
PROJECTION 	COLOR VARIATIONS MAY OCCUR	CSNULL-FS01	SCALE: NONE CAD FILE: CSNULL9FF.SLDDRW	SHEET 1 OF 1