_	8 7 6	5	★ 4	3	2	1	
	THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.			REV	REVISIONS	DATE	APPROVED
	WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.		A INITIAL RELEASE		5/28/08	D.GRIFFIN	
] —		PERATING TEMPERATURE RANGE AND PACKAC D THUMBSCREW FROM STEEL TO BRASS	GING 10/1/09 1/19/10	D.FRISIELLO D.FRISIELLO	
D							D
		00000					
			$\mathbb{Q}[$				
			<u>ــــــــــــــــــــــــــــــــــــ</u>				
	2X, THUMBSCREW, 4-40						
			► 2X, Ø.27[6.8] –	.82[20.9]		
С		b					C
	Ţ						
	1.06[27]		.50[12.8	1			
				1			
	<u> </u>	7					4
							7
		── (.984[25]					
		- (.704 [23]	,				
В							В
-							
	NOTES:						
	MATERIAL:						
	HOUSING: ABS, BLACK GASKET: EPDM, BLACK	RoHS Compliant ✓					
	THUMBSCREW: BRASS, WITH NICKEL PLATING		UNLESS OTHERWISE SPECIFIED,	APPROVALS DATE		45 BEECHW	OOD DRIVE
	AND DIAMOND KNURLING.		DIMENSIONS ARE IN INCHES [mm]	DRAWN BY D.FRISIELLO 5/22/08		NORTH AN	DOVER, MA 845
Α	WATERPROOF RATING: IP67.		DIMENSIONAL TOLERANCES:	D.FRISIELLO 5/22/08 CHECKED BY D.FORTIN 5/22/08	CATEGORY	01	A
	OPERATING TEMPERATURE RANGE: -40°C TO +105°	C.	.X = ±.1 .XX = ±.02 .XXX = ±.005	APPROVED BY S.SMITH 5/22/08	D-SUB		
		ANGULAR TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES	PRODUCT DESCRIPTION			
	COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PA ACCORDANCE WITH L-COM SPECIFICATION PS-0	$ALL = \pm 1^{\circ}$	UNDIMENSIONED FEATURES MAY VARY	COVER, WATERPROOF, DB9 / H		HD15	
			PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE FSCM NO. DWG. NO. 43321 V	VPSD1-CVR	C REV.
				MATOCCUR	SCALE: NONE CAD FILE: WPSD1-CVI		SHEET 1 OF 1
L	8 7 6	5	4	3	2	1	
		-	•	-		-	