

Crimp Tool Cross Reference Chart

Use this chart to find the correct ferrule and center conductor crimp size as well as the recommended economy, deluxe and deluxe kit crimp tool for each of the connector model numbers listed.

If a specific type is not listed, please visit our website at www.L-com.com for the latest information or call our technical support group at 800-343-1455 for assistance.

CONNECTOR P/N	CRIMP SIZE		CRIMP TOOL		
	FERRULE	CENTER COND.	ECONOMY	DELUXE	DELUXE KIT
BAC518	0.213	0.068	HT106D	HT301A	HT330K
BAC519	0.213	0.068	HT106D	HT301A	HT330K
BAC522	0.213	0.068	HT106D	HT301A	HT330K
BAC524	0.213	0.068	HT106D	HT301A	HT330K
BAC836A-58	0.213	0.068	HT106D	HT301A	HT330K
BAC836A-58P	0.213	0.068	HT106D	HT301A	HT330K
BIF-83	0.231	0.068	HT106D	HT301A	HT330K
BAC523	0.178	0.068	N/A	HT301J	HT330K
BAC526	0.178	0.068	N/A	HT301J	HT330K
BAC527	0.178	0.068	N/A	HT301J	HT330K
BAC528	0.178	0.068	N/A	HT301J	HT330K
BAC836B-74	0.178	0.068	N/A	HT301J	HT330K
BAC893-58	0.213	0.068	HT106D	HT301A	HT330K
BAC893-59	0.255	0.068	HT106D	HT301A	HT330K
BAC908-59	0.255	0.068	HT106D	HT301A	HT330K
BAC934-59	0.255	0.068	HT106D	HT301A	HT330K
BAC706	0.255	0.068	HT106D	HT301A	HT330K
BAC709	0.255	N/A	HT106D	HT301A	HT330K
BAC012	0.324	N/A	HT106H	HT301D	HT330K
BAC013	0.319	N/A	HT106H	HT301C	HT330K
BAC027	0.255	0.068	HT106D	HT301A	HT330K
BAC027A	0.255	0.068	HT106D	HT301A	HT330K
BAC028	0.255	0.068	HT106D	HT301A	HT330K
BAC029	0.324	0.068	N/A	HT301D	HT330K
BAC030	0.324	0.255	N/A	HT301D	HT330K
BAC031	0.324	0.255	N/A	HT301D	HT330K
BAC032	0.319	N/A	HT106H	HT301C	HT330K
BAC520	0.255	0.068	HT106D	HT301A	HT330K
BAC836A-59	0.255	0.068	HT106D	HT301A	HT330K

CONNECTOR P/N	CRIMP SIZE		CRIMP TOOL		
	FERRULE	CENTER COND.	ECONOMY	DELUXE	DELUXE KIT
BAC836B-87	0.213	0.068	HT106D	HT301A	HT330K
BAC042	0.319	N/A	HT106H	HT301C	HT330K
BAC02	0.213	N/A	HT106D	HT301A	HT330K
BAC02A	0.128	N/A	N/A	HT301J	HT330K
BAC03	0.213	0.042	N/A	HT301G	HT330K
BAC03A	0.128	0.042	N/A	HT301J	HT330K
BAC04	0.213	0.042	N/A	HT301G	HT330K
BAC05	0.213	0.042	N/A	HT301G	HT330K
BAC05A	0.128	0.042	N/A	HT301J	HT330K
BAC02-G	0.213	N/A	HT106D	HT301A	HT330K
BAC02A-G	0.128	N/A	N/A	HT301J	HT330K
BAC03-G	0.213	0.042	N/A	HT301G	HT330K
BAC03A-G	0.128	0.042	N/A	HT301J	HT330K
BAC06A	0.128	0.042	N/A	HT301J	HT330K
BAC410	0.213	N/A	HT106D	HT301A	HT330K
BAC8015	0.213	N/A	HT106D	HT301A	HT330K
BAC525	0.213	N/A	HT106D	HT301A	HT330K
BAC500	0.213	N/A	HT106D	HT301A	HT330K
BAC501	0.213	N/A	HT106D	HT301A	HT330K
BAC502	0.128	0.042	N/A	HT301J	HT330K
BAC503	0.137	N/A	N/A	HT301G	HT330K
BAC-CFS6U	0.324	N/A	HT106H	HTS3162CT	N/A
BAC-CFS59U	0.324	N/A	HT106H	HTS3162CT	N/A
BAC-CFS6SUV	0.360	N/A	HT106H	HTS3162CT	N/A
BAC-CFS59SUV	0.360	N/A	HT106H	HTS3162CT	N/A
BAC-EX6	Compression	N/A	N/A	HTS-EX	N/A
BAC-EX59	Compression	N/A	N/A	HTS-EX	N/A
BAC700-6	.319	N/A	HT106H	HT301C	HT330K
BAC700-59	.262	N/A	HT106D	HT301A	HT330K

CONNECTOR P/N	FERRULE	CRIMP TOOL	CENTER COND.	CRIMP TOOL
BAC-UPL2000-D2B	0.255	HTS-CT4L & HTS-CD3-21	0.042	HT010-0055
BAC-UPL2000-D8B	0.255	HTS-CT4L & HTS-CD3-21	0.042	HT010-0055

CONNECTOR P/N	FERRULE	CRIMP TOOL	CENTER COND.	CRIMP TOOL
BAC-UPL220-025	0.255	HTS-CT4L & HTS-CD3-11	0.042	HT010-0055
BAC-UPL220-026	0.178	HTS-CT4L & HTS-CD3-11	0.042	HT010-0055

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

RoHS Economy Crimping Tools - Common Crimp Sizes for Connectors and Center Pins

These heavy-duty crimping tools are economically priced and easy to use. Leverage action produces an enormous force to properly crimp a perfect hex every time. An adjustable cam is added to keep the tool in full conformance with the required tolerance. Tools accept the most popular crimp connector types. HT106D hex sizes are .068", .213" and .255". HT106H hex sizes are .322" and .359".

HT106D	9" Lever Type Coaxial Crimp Tool (.068", .213", .255")	29.95	27.55	25.16	22.76	20.37
HT106H	9" Lever Type Coaxial Crimp Tool (.322", .359")	29.95	27.55	25.16	22.76	20.37

Deluxe Full Cycle Ratchet with Hex Crimping Tools

Your choice of seven similar crimp tools equipped with specific die sets to perform a wide variety of crimping functions to fit your needs.

HT301A	Deluxe Crimp Tool with .256", .213" and .068" Hex Die	31.95	29.39	26.84	24.28	21.73
HT301C	Deluxe Crimp Tool with .319", .256", .213" and .068" Hex Die	39.95	36.75	33.56	30.36	27.17
HT301D	Deluxe Crimp Tool with .324", .256", .213" and .068" Hex Die	39.95	36.75	33.56	30.36	27.17
HT301G	Deluxe Crimp Tool with .255", .213", .137", .100", .069", .043" Hex Die	36.95	33.99	31.04	28.08	25.13
HT301J	Deluxe Crimp Tool with .178", .151", .128", .078", .068", .042" Hex Die	36.95	33.99	31.04	28.08	25.13
HT301K	Deluxe Crimp Tool with .429", .128" and .100" Hex Die	41.95	38.59	35.24	31.88	28.53
HT230A	Deluxe Crimp Tool with .255", .213", .187" and .068" Hex Die	34.95	32.15	29.36	26.56	23.77
HT-CRIMP02	Deluxe Crimp Tool with .028", .039", .047", .100", .128" and .151" Hex Die	24.99	22.49	19.99	17.49	14.99
HT-CRIMP03	Deluxe Crimp Tool with .100", .128" and .429" Hex Die	34.99	31.49	27.99	24.49	20.99
HT-CRIMP04	Deluxe Crimp Tool with .068", .213", .256" and .324" Hex Die	24.99	22.49	19.99	17.49	14.99
HT-CRIMP600	Deluxe Crimp Tool with .610" Hex Die	29.99	26.99	23.99	20.99	17.99

Deluxe Full Cycle Ratchet Crimp Tool Kit

Housed in rugged, high impact cases these handy deluxe ratchet crimp and strip tool kits can satisfy most coaxial crimping needs. These kits include ratchet tool, interchangeable dies, cable cutter and rotary cable stripper. See www.L-com.com for complete kit contents.

HT330K	Deluxe Crimp Tool Kit, for use with RG Type Cable	144.95	133.35	121.76	110.16	98.57
HT-KIT-01	Deluxe Crimp Tool Kit, for use with Low-Loss and RG Type Cable	89.99	86.39	82.79	76.49	67.49



Helpful videos

How-to videos help with some of today's popular product applications. L-com.com/Tips