

Weatherproof Enclosures

Enclosure Size	NEMA Rating	NEW UL® Listed	Blank Mtg. Plate	Pre-Drilled Mtg. Plate	DIN Mtg. Rails	Heater	Cooling Fan	Solid State Controller	802.3af Compliant	Vented Enclosure	Item
120 VAC ENCLOSURES											
14" x 10" x 4"	3R									✓	NBP141004-10V
	3R						✓			✓	NBP141004-10F
	3R										NBP141004-100
	3R										NBP141004-100-4
14" x 12" x 7"	3R	Pending		✓							NB141207-100
	4X			✓		✓					NB141207-1H0
	4X	Pending		✓		✓		✓			NB141207-1H0S
	3R			✓			✓			✓	NB141207-10F
	3R	Pending		✓			✓	✓		✓	NB141207-10FS
	3R			✓			✓	✓		✓	NB141207-10FSD
	3R			✓		✓	✓			✓	NB141207-1HF
	3R			✓		✓	✓	✓		✓	NB141207-1HFS
	3R	Pending		✓		✓	✓	✓		✓	NB141207-1HFS-JL
	3R			✓						✓	NB141207-10V
18" x 16" x 8"	4X			✓							NB181608-100
	4X			✓		✓					NB181608-1H0
	4X			✓		✓		✓			NB181608-1H0
	3R			✓			✓			✓	NB181608-10F
	3R			✓			✓	✓		✓	NB181608-10FS
	3R			✓			✓	✓		✓	NB181608-10FSD
	3R			✓		✓	✓			✓	NB181608-1HF
	3R			✓		✓	✓	✓		✓	NB181608-1HFS
	3R			✓						✓	NB181608-10V
240 VAC ENCLOSURES											
14" x 12" x 7"	4X			✓			✓			✓	NB141207-2H0
	3R			✓			✓			✓	NB141207-20F
	3R			✓		✓	✓			✓	NB141207-2HF
18" x 16" x 8"	3R			✓			✓			✓	NB181608-20F
	4X			✓			✓			✓	NB181608-2H0
	3R			✓		✓	✓			✓	NB181608-2HF
240 VAC ENCLOSURES WITH EURO PLUGS											
14" x 10" x 4"	3R										NBP141004-E00
	3R										NBP141004-E00-4
	3R			✓			✓			✓	NBP141004-E0F
	3R									✓	NBP141004-E0V
14" x 12" x 7"	3R			✓		✓					NB141207-EH0
	3R			✓		✓	✓			✓	NB141207-EHF
	3R			✓							NB141207-E00
	3R			✓						✓	NB141207-E0V
18" x 16" x 8"	3R			✓		✓					NB181608-EH0
	3R			✓		✓	✓			✓	NB181608-EHF
	3R			✓			✓			✓	NB181608-E0F
	3R			✓							NB181608-E00
	3R			✓						✓	NB181608-E0V
POWER-OVER-ETHERNET ENCLOSURES											
14" x 10" x 4"	3R									✓	NBP141004-40V
	3R						✓			✓	NBP141004-40F
14" x 12" x 7"	3R			✓						✓	NB141207-400
	3R			✓			✓			✓	NB141207-40F
	3R			✓			✓	✓		✓	NB141207-40FS
	4X			✓			✓		✓	✓	NB141207-40FAF
	4X			✓			✓	✓	✓	✓	NB141207-40FSAF
	3R			✓						✓	NB141207-40V
	3R			✓							NB181608-400
18" x 16" x 8"	3R			✓			✓			✓	NB181608-40F
	3R			✓			✓	✓		✓	NB181608-40FS
	3R			✓						✓	NB181608-40V
	4X			✓			✓		✓	✓	NB181608-40FAF
	4X			✓			✓	✓	✓	✓	NB181608-40FSAF
	3R			✓						✓	NB181608-40V
12 VDC ENCLOSURES											
14" x 12" x 7"	4X			✓							NB141207-500
	3R			✓			✓			✓	NB141207-50F
	3R			✓						✓	NB141207-50V
18" x 16" x 8"	3R			✓							NB181608-500
	3R			✓			✓			✓	NB181608-50F
	3R			✓						✓	NB181608-50V