

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**DVI Products**

DVI (Digital Video Interface) is a widely used interface specifically designed for the transmission of digital video signals. L-com's DVI cable assemblies and adapters are offered in various interface combinations and gender configurations to address a broad range of connection applications.

**DVI Cable Assemblies - Fully Molded with Ferrites**

This series of DVI cable assemblies features a molded integrated ferrite on both ends for EMI/RFI protection and a fully molded and shielded backshell. Offered in 4 standard lengths not exceeding the recommended 5 meter maximum for DVI cables.

**✓RoHS DVI-I Single Link Cable Assembly with Ferrites**

<a href="#">CTLDVI-ISL-MM-3</a>	DVI Cable, DVI-I Single Link, Male / Male, 3.0 ft	16.61	15.28	13.95	12.62	11.29
<a href="#">CTLDVI-ISL-MM-5</a>	DVI Cable, DVI-I Single Link, Male / Male, 5.0 ft	18.26	16.80	15.34	13.88	12.42
<a href="#">CTLDVI-ISL-MM-10</a>	DVI Cable, DVI-I Single Link, Male / Male, 10.0 ft	22.21	20.43	18.66	16.88	15.10
<a href="#">CTLDVI-ISL-MM-15</a>	DVI Cable, DVI-I Single Link, Male / Male, 15.0 ft	26.21	24.11	22.02	19.92	17.82

**✓RoHS DVI-I Dual Link Cable Assembly with Ferrites**

<a href="#">CTLDVI-I-MM-3</a>	DVI Cable, DVI-I Dual Link, Male / Male, 3.0 ft	18.34	16.87	15.41	13.94	12.47
<a href="#">CTLDVI-I-MM-5</a>	DVI Cable, DVI-I Dual Link, Male / Male, 5.0 ft	20.76	19.10	17.44	15.78	14.12
<a href="#">CTLDVI-I-MM-10</a>	DVI Cable, DVI-I Dual Link, Male / Male, 10.0 ft	26.71	24.57	22.44	20.30	18.16
<a href="#">CTLDVI-I-MM-15</a>	DVI Cable, DVI-I Dual Link, Male / Male, 15.0 ft	32.66	30.05	27.43	24.82	22.21

**✓RoHS DVI-D Single Link Cable Assembly with Ferrites**

<a href="#">CTLDVIMM-3</a>	DVI Cable, DVI-D Single Link, Male / Male, 3.0 ft	11.16	10.27	9.37	8.48	7.59
<a href="#">CTLDVIMM-5</a>	DVI Cable, DVI-D Single Link, Male / Male, 5.0 ft	12.13	11.16	10.19	9.22	8.25
<a href="#">CTLDVIMM-10</a>	DVI Cable, DVI-D Single Link, Male / Male, 10.0 ft	14.47	13.31	12.15	11.00	9.84
<a href="#">CTLDVIMM-15</a>	DVI Cable, DVI-D Single Link, Male / Male, 15.0 ft	16.82	15.47	14.13	12.78	11.44

**✓RoHS DVI-D Dual Link Cable Assembly with Ferrites**

<a href="#">CTLDVI-DL-MM-3</a>	DVI Cable, DVI-D Dual Link, Male / Male, 3.0 ft	15.34	14.11	12.89	11.66	10.43
<a href="#">CTLDVI-DL-MM-5</a>	DVI Cable, DVI-D Dual Link, Male / Male, 5.0 ft	16.89	15.54	14.19	12.84	11.49
<a href="#">CTLDVI-DL-MM-10</a>	DVI Cable, DVI-D Dual Link, Male / Male, 10.0 ft	20.61	18.96	17.31	15.66	14.01
<a href="#">CTLDVI-DL-MM-15</a>	DVI Cable, DVI-D Dual Link, Male / Male, 15.0 ft	24.32	22.37	20.43	18.48	16.54

**DVI Adapter Cables - Adapt from DVI to HD15 and DFP**

This series of cable assemblies allows adaptation from DVI to compatible HD15 and DFP interfaces.

**✓RoHS DVI-A to HD15 Cable Assembly with Ferrites**

<a href="#">CTLDVI-HD-MM-3</a>	DVI Cable, DVI-A to HD15, Male / Male, 3.0 ft	13.13	12.08	11.03	9.98	8.93
<a href="#">CTLDVI-HD-MM-5</a>	DVI Cable, DVI-A to HD15, Male / Male, 5.0 ft	14.21	13.07	11.94	10.80	9.66
<a href="#">CTLDVI-HD-MM-10</a>	DVI Cable, DVI-A to HD15, Male / Male, 10.0 ft	16.87	15.52	14.17	12.82	11.47
<a href="#">CTLDVI-HD-MM-15</a>	DVI Cable, DVI-A to HD15, Male / Male, 15.0 ft	20.03	18.43	16.83	15.22	13.62

**✓RoHS DVI-D to DFP Cable Assembly with Ferrites**


<a href="#">CTLDVIMR-3</a>	DVI Cable, DVI-D to DFP, Male / Male, 3.0 ft	20.00	18.40	16.80	15.20	13.60
<a href="#">CTLDVIMR-5</a>	DVI Cable, DVI-D to DFP, Male / Male, 5.0 ft	21.50	19.78	18.06	16.34	14.62
<a href="#">CTLDVIMR-10</a>	DVI Cable, DVI-D to DFP, Male / Male, 10.0 ft	25.25	23.23	21.21	19.19	17.17
<a href="#">CTLDVIMR-15</a>	DVI Cable, DVI-D to DFP, Male / Male, 15.0 ft	29.00	26.68	24.36	22.04	19.72

**DVI KVM (Keyboard, Video, Mouse) Cables - Mini DIN 6 Connectors**

This series of KVM cables is offered transitioning the video from DVI to HD15. Both male to male and male to female configurations are available.

**✓RoHS DVI/HD15 KVM Cable Assembly Combine DVI-A with HD15 + 2 Mini DIN 6 Connectors**

<a href="#">CTLDVIKVM-2</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6, Male / Male, 2.0m	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVIKVM-3</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6, Male / Male, 3.0m	45.00	41.40	37.80	34.20	30.60
<a href="#">CTLDVIKVM-5</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6, Male / Male, 5.0m	55.00	50.60	46.20	41.80	37.40
<a href="#">CTLDVIKVMF-2</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6, Male / Female, 2.0m	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVIKVMF-3</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6, Male / Female, 3.0m	45.00	41.40	37.80	34.20	30.60
<a href="#">CTLDVIKVMF-5</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6, Male / Female, 5.0m	55.00	50.60	46.20	41.80	37.40




CTLDVI-ISL-MM  
CTLDVI-I-MM  
CTLDVIMM  
CTLDVI-DL-MM

CTLDVI-HD-MM

CTLDVIMR

**Did you know...**

DVI-A cables can be used with DVI-I interfaces/cables?



CTLDVIKVM

**Tip**

**What is the difference between DVI Single Link and Dual Link?**

DVI dual link, as the name implies, has more conductors than the DVI single link for transmitting signal. Single link DVI supports a maximum bandwidth of 165 MHz (1920 x 1080 at 60 Hz, 1280 x 1024 at 85 Hz) and utilizes 18 of the 24 available pins. Dual link DVI utilizes all 24 available pins and supports 2x 165 MHz maximum bandwidth (2048 x 1536 at 60 Hz, 1920 x 1080 at 85 Hz).

DVI Single Link

DVI Dual Link

**Same day shipping**  
Orders placed before 4:00 EST ship the same day.