


CTC Series

**CTC Construction Detail**



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**RoHS Twinaxial BNC Cables - Feature Polarized/Stepped Keyway and Crimp Design**

This Twin BNC cable series accommodates the need for low level signal patching and balanced line applications. Fittings have polarized, stepped keyways that look like, but do not match traditional BNC coaxial connectors. Twin BNC connectors are constructed of machined brass with a non-tarnish nickel finish and gold plated contacts.

Twinaxial		NOMINAL ATTENUATION		
		MHz	db/100ft	db/100m
• Center Conductors: 20 (7x28) AWG tinned copper		50	5.0	16.4
• Shielding: Tinned copper braid + foil (100% coverage)		100	7.5	24.6
• Insulation: Polyethylene		200	11.0	36.1
• Jacket: Blue PVC		400	16.0	52.5
• Operating Temperature: -20°C - +80°C				

**78 Ohm Impedance**

CTC-1	78 Ohm Twinaxial Cable, Twin BNC Male / Male, 1.0ft (0.3m)	44.00	42.24	40.48	38.72	36.96
CTC-2	78 Ohm Twinaxial Cable, Twin BNC Male / Male, 2.0ft (0.6m)	45.00	43.20	41.40	39.60	37.80
CTC-3	78 Ohm Twinaxial Cable, Twin BNC Male / Male, 3.0ft (0.9m)	47.00	45.12	43.24	41.36	39.48
CTC-5	78 Ohm Twinaxial Cable, Twin BNC Male / Male, 5.0ft (1.5m)	51.00	48.96	46.92	44.88	42.84
CTC-7.5	78 Ohm Twinaxial Cable, Twin BNC Male / Male, 7.5ft (2.3m)	55.00	52.80	50.60	48.40	46.20
CTC-10	78 Ohm Twinaxial Cable, Twin BNC Male / Male, 10.0ft (3.0m)	59.00	56.64	54.28	51.92	49.56

**RoHS Stainless Steel Wall Plates - Unbreakable and Offer An Enhanced Appearance**

Wall plates that accept a variety of termination devices are found to be useful by many installers. Wall plates also provide a more organized accommodation to your day-to-day cabling needs. Furthermore, stainless steel gives a commercial appearance that is sometimes more acceptable in today's business office environment. The variety we offer fills most installation needs.

WPC1	Stainless Wall Plate, One 0.5" (1.3cm) dia. D-hole	1.95	1.83	1.72	1.60	1.48
WPC2	Stainless Wall Plate, Two 0.5" (1.3cm) dia. D-holes	2.25	2.11	1.98	1.85	1.71
WPC10	Stainless Wall Plate, One 0.75" (1.9cm) dia. D-hole	1.95	1.83	1.72	1.60	1.48
WPD3	Stainless Wall Plate, One DB25 Opening and One 0.5" (1.3cm) dia. D-hole	2.60	2.44	2.29	2.13	1.98

**RoHS Panel Mount Receptacle Connectors**

These series of connectors are intended for panel mounting with discrete receptacle terminations. Offered in BNC, RCA and Type N interfaces with various mounting configurations.

BAC1501	BNC Male Bulkhead	2.95	2.71	2.48	2.24	2.01
BAC1503	BNC Female Bulkhead	2.95	2.71	2.48	2.24	2.01
BAC930	BNC Female Bulkhead	5.95	5.47	5.00	4.52	4.05
BAC440	RCA Female Insulated Bulkhead	3.95	3.63	3.32	3.00	2.69
BAC260	BNC Female, 4 Hole Flange	2.95	2.71	2.48	2.24	2.01
BAN113	Type N Female, 4 Hole Flange	4.95	4.55	4.16	3.76	3.37
BAC70A	BNC Female Bulkhead	2.95	2.71	2.48	2.24	2.01
BAC16	SMA Female Bulkhead	4.95	4.55	4.16	3.76	3.37

**Deluxe Coaxial Adapter Kit**

This deluxe adapter kit features a universal coupling which allows interchangeable connections between all 30 individual interfaces resulting in 108 possible combinations. Supplied in a zippered storage case that is ideal for portable use.

BAK300	Deluxe Coaxial Adapter Kit	125.00	120.00	115.00	110.00	105.00
--------	----------------------------	--------	--------	--------	--------	--------

**Premium Coaxial Adapter Kit**

L-com's premium adapter kit features a universal coupling which allows interchangeable connections between all 40 individual interfaces resulting in 192 possible combinations. Supplied in a zippered storage case that is ideal for portable use.

BAK400	Premium Coaxial Adapter Kit	150.00	144.00	138.00	132.00	126.00
--------	-----------------------------	--------	--------	--------	--------	--------

**SMA Interseries Adapter Kit**

This handy adapter kit offers a super value versus buying parts separately. Kit contains SMA interseries adapters all stored in a multi compartment storage case. Adapters are machined and plated for corrosion resistance and long life.

BA1200K	SMA Interseries Adapter Kit	49.95	46.95	43.96	40.96	37.96
---------	-----------------------------	-------	-------	-------	-------	-------

**BNC Within Series Adapter Kit**


This useful adapter kit offers a super value to buying parts separately. Kit includes various BNC adapters as well as 3 port tees and right angle configurations all stored in a multi compartment storage case. Adapters are machined and plated for corrosion resistance and long life.

BA1700K	BNC Adapter Kit	39.95	37.55	35.16	32.76	30.36
---------	-----------------	-------	-------	-------	-------	-------


**BNC Interseries Adapter Kit**

This handy adapter kit offers a super value versus buying parts separately. This kit includes various BNC interseries adapters all stored in a multi compartment storage case. Adapters are machined and plated for corrosion resistance and long life.

BA1800K	BNC Interseries Adapter Kit	39.95	37.55	35.16	32.76	30.36
---------	-----------------------------	-------	-------	-------	-------	-------




WPC1



WPC2



WPC10



WPD3



BAC1501



BAC1503



BAC930

Fits in a .375" hole



BAC440



BAC260



BAN113



BAC70A



BAC16



BAK300

BAK400

BA1200K

BA1700K

BA1800K

