



Premium Category 6 RJ45 to RJ45 Shielded Patch Cords

Category 6 has become the de facto standard when installing new network cabling. With high bandwidth applications on the rise and Ethernet network deployments venturing into new areas such as factory environments, the need for shielded Cat 6 cable assemblies has also increased. L-com has stepped up to this new demand and created a line of high performance Cat 6 patch cords that feature a 100% foil shield and the option of either a PVC or Zero Halogen jacket.



Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
RoHS Category 6 Shielded Patch Cords with PVC Jacket							
This series features a RoHS compliant PVC jacket and a 100% foil shield. The four pair 26 AWG stranded Cat 6 cable is terminated with L-com's unique shielded Cat 6 plugs, with a fully crimped shield termination that doubles as a strain relief.							
TRD695SCR-1	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 1.0ft (0.3m)	Lt. Gray	8.95	8.77	8.41	7.88	6.71
TRD695SCR-2	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 2.0ft (0.6m)	Lt. Gray	9.95	9.75	9.35	8.76	7.46
TRD695SCR-3	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 3.0ft (0.9m)	Lt. Gray	10.95	10.73	10.29	9.64	8.21
TRD695SCR-5	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 5.0ft (1.5m)	Lt. Gray	12.95	12.69	12.17	11.40	9.71
TRD695SCR-7	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 7.0ft (2.1m)	Lt. Gray	14.95	14.65	14.05	13.16	11.21
TRD695SCR-10	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 10.0ft (3.0m)	Lt. Gray	17.95	17.59	16.87	15.80	13.46
TRD695SCR-15	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 15.0ft (4.6m)	Lt. Gray	22.95	22.49	21.57	20.20	17.21
TRD695SCR-25	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 25.0ft (7.6m)	Lt. Gray	32.95	32.29	30.97	29.00	24.71
TRD695SCR-50	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 50.0ft (15.2m)	Lt. Gray	57.95	56.79	54.47	51.00	43.46
TRD695SCR-75	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 75.0ft (22.9m)	Lt. Gray	82.95	81.29	77.97	73.00	62.21
TRD695SCR-100	Shielded Cat. 6 Patch Cord, RJ45 / RJ45, 100.0ft (30.4m)	Lt. Gray	107.95	105.79	101.47	95.00	80.96

RoHS Category 6 Shielded Patch Cords with LSZH Jacket

This series features a LSZH jacket and a 100% foil shield. The four pair 26 AWG stranded Cat 6 cable is terminated with L-com's unique shielded Cat 6 plugs, with a fully crimped shield termination that doubles as a strain relief.

TRD695SZ-1	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 1.0ft (0.3m)	Lt. Gray	14.95	14.35	13.75	13.16	12.56
TRD695SZ-2	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 2.0ft (0.6m)	Lt. Gray	15.95	15.31	14.67	14.04	13.40
TRD695SZ-3	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 3.0ft (0.9m)	Lt. Gray	16.95	16.27	15.59	14.92	14.24
TRD695SZ-5	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 5.0ft (1.5m)	Lt. Gray	18.95	18.19	17.43	16.68	15.92
TRD695SZ-7	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 7.0ft (2.1m)	Lt. Gray	20.95	20.11	19.27	18.44	17.60
TRD695SZ-10	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 10.0ft (3.0m)	Lt. Gray	23.95	22.99	22.03	21.08	20.12
TRD695SZ-15	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 15.0ft (4.6m)	Lt. Gray	28.95	27.79	26.63	25.48	24.32
TRD695SZ-25	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 25.0ft (7.6m)	Lt. Gray	38.95	37.39	35.83	34.28	32.72
TRD695SZ-50	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 50.0ft (15.2m)	Lt. Gray	63.95	61.39	58.83	56.28	53.72
TRD695SZ-75	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 75.0ft (22.9m)	Lt. Gray	88.95	85.39	81.83	78.28	74.72
TRD695SZ-100	Shielded Cat. 6 LSZH Patch Cord, RJ45 / RJ45, 100.0ft (30.4m)	Lt. Gray	113.95	109.39	104.83	100.28	95.72

RoHS Extreme Hi-Flex Oil Resistant Category 5E Patch Cords

This series features 26 AWG stranded conductors and a braid and foil shield. The outer jacket is low-friction halogen-free PUR. This cable has been tested to 10 million flex cycles.

TRD877HF-1	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 1.0ft (0.3m)	Teal	36.95	35.47	33.99	32.52	31.04
TRD877HF-2	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 2.0ft (0.6m)	Teal	39.90	38.30	36.71	35.11	33.52
TRD877HF-3	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 3.0ft (0.9m)	Teal	42.85	41.14	39.42	37.71	35.99
TRD877HF-5	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 5.0ft (1.5m)	Teal	48.75	46.80	44.85	42.90	40.95
TRD877HF-7	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 7.0ft (2.1m)	Teal	54.65	52.46	50.28	48.09	45.91
TRD877HF-10	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 10.0ft (3.0m)	Teal	63.50	60.96	58.42	55.88	53.34
TRD877HF-15	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 15.0ft (4.6m)	Teal	78.25	75.12	71.99	68.86	65.73
TRD877HF-25	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 25.0ft (7.6m)	Teal	107.75	103.44	99.13	94.82	90.51
TRD877HF-50	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 50.0ft (15.2m)	Teal	181.50	174.24	166.98	159.72	152.46
TRD877HF-75	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 75.0ft (22.9m)	Teal	255.25	245.04	234.83	224.62	214.41
TRD877HF-100	Shielded Cat. 5E Extreme Hi-Flex Patch Cord, RJ45 / RJ45, 100.0ft (30.4m)	Teal	329.00	315.84	302.68	289.52	276.36

RoHS Hi-Flex Oil Resistant Category 5E Patch Cords

This series features 26 AWG stranded conductors and a braided shield. The outer jacket is low-friction halogen-free PUR that is perfect for cable track applications.

TRD855HF-1	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 1.0ft (0.3m)	Teal	34.95	33.55	32.15	30.76	29.36
TRD855HF-2	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 2.0ft (0.6m)	Teal	37.90	36.38	34.87	33.35	31.84
TRD855HF-3	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 3.0ft (0.9m)	Teal	40.85	39.22	37.58	35.95	34.31
TRD855HF-5	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 5.0ft (1.5m)	Teal	46.75	44.88	43.01	41.14	39.27
TRD855HF-7	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 7.0ft (2.1m)	Teal	52.65	50.54	48.44	46.33	44.23
TRD855HF-10	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 10.0ft (3.0m)	Teal	61.50	59.04	56.58	54.12	51.66
TRD855HF-15	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 15.0ft (4.6m)	Teal	76.25	73.20	70.15	67.10	64.05
TRD855HF-25	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 25.0ft (7.6m)	Teal	105.75	101.52	97.29	93.06	88.83
TRD855HF-50	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 50.0ft (15.2m)	Teal	179.50	172.32	165.14	157.96	150.78
TRD855HF-75	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 75.0ft (22.9m)	Teal	253.25	243.12	232.99	222.86	212.73
TRD855HF-100	Shielded Cat. 5E Hi-Flex Patch Cord, RJ45 / RJ45, 100.0ft (30.4m)	Teal	327.00	313.92	300.84	287.76	274.68

Best Seller

TRD695SCR

SHIELDED CATEGORY 6

- 4 pair 26 AWG stranded
- PVC jacket
- Foil shielding

TRD695SZ

SHIELDED CATEGORY 6

- 4 pair 26 AWG stranded
- LSZH jacket
- Foil shielding

TRD877HF

EXTREME HIGH-FLEX SHIELDED CATEGORY 5E

- 4 pair 26 AWG stranded
- Zero Halogen jacket
- Double shielded foil
- Tested to 10 million flex cycles

TRD855HF

HIGH-FLEX SHIELDED CATEGORY 5E

- 4 pair 26 AWG stranded
- Oil resistant jacket
- Braid shielding
- Tested to 2.5 million flex cycles



Technical resources

Free tips, tutorials and downloads help you learn all about connectivity. Visit L-com.com/Resources